


Surface Mount Schottky Barrier Diode



Features:

- Low Turn-On Voltage
- Fast Switching
- PN Junction Guard Ring for Transient And BAS70 BAS70-04 ESD Protection
- Ultra-Small Surface Mount Package
- Also Available in Lead Free Version


Applications:

- High speed switching applications.
- Circuit protecting : SOT-23
- Voltage clamping


Maximum Ratings:

T_A = 25°C unless otherwise specified.


Characteristic	Symbol	Limits	Unit
RMS reverse voltage	V _{R(RMS)}	49	V
Repetitive peak reverse voltage Working peak reverse voltage Diode reverse voltage	V _{RRM} V _{RWM} V _R	70	V
Forward continuous current	I _F	70	mA
Non-Repetitive peak forward surge current at t _p <1s	I _{FSM}	100	mA
Power dissipation	P _D	200	mW
Thermal resistance, junction to ambient air	R _{θJA}	625	°C/W
Junction and storage temperature range	T _j , T _{stg}	-65 to +150	°C



BAS70



BAS70-05



SOT-23

Surface Mount Schottky Barrier Diode





Electrical Characteristics:

$T_A = 25^\circ\text{C}$ unless otherwise specified.


Characteristic	Symbol	Test conditions	Min.	Max.	Unit
Reverse breakdown voltage	$V_{(BR)R}$	$I_{(BR)} = 10\mu\text{A}$	70	-	V
Reverse leakage current	I_R	$t_P < 300\mu\text{s}$, $V_R = 50\text{V}$	-	100	nA
Forward voltage	V_F	$t_P < 300\mu\text{s}$, $I_F = 1\text{mA}$ $t_P < 300\mu\text{s}$, $I_F = 15\text{mA}$	-	410 1,000	mV
Junction capacitance	C_j	$V_R = 0\text{V}$, $f = 1\text{MHz}$	-	2	pF
Reverse recovery time	t_{rr}	$I_F = I_R = 10\text{mA}$ to $I_R = 1\text{mA}$, $R_L = 100\Omega$	-	5	nS

Typical Characteristics:


$T_A = 25^\circ\text{C}$ unless otherwise specified.



Surface Mount Schottky Barrier Diode




V_R, REVERSE VOLTAGE (V)
Fig. 3 Typical Capacitance



T_A, AMBIENT TEMPERATURE (°C)
Fig. 4 Power Derating Curve, Total Package

Package Outline:

Plastic surface mounted package




SOT-23		
Dim.	Min.	Max.
A	2.85	2.95
B	1.25	1.35
C	1 Typ.	
D	0.37	0.43
E	0.35	0.48
G	1.85	1.95
H	0.02	0.1
J	0.1 Typ.	
K	2.35	2.45

Dimensions : Millimetres

Surface Mount Schottky Barrier Diode



Soldering Footprint:



Dimensions : Millimetres

Package Information:

Device	Package	Shipping
BAS70-05-7-F BAS70-7-F	SOT-23	3,000 / Tape & Reel

Part Number Table

Description	Part Number
Surface Mount Schottky Barrier Diode	BAS70-05-7-F
	BAS70-7-F

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.