





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AL	2		B1	REVISED PER ECO-11-005139	11APR2011	RK	HMR
			C	SEE ECR 11-010607	17MAY2011	JS	LB
			C1	ECR-14-007191	29OCT2014	SK	JP
			C2	ECR-14-017645	28NOV2014	SK	JP




WIRE CROSS SECTION (mm²)

	SINGLE WIRE	0.35	0.50	0.75	1.00
		X	X		
		X	X	X	
		X			
		X			

WIRE CRIMP SELECTION TABLE

WIRE: "F" CRIMP
INSULATION: OVERLAPPING CRIMP

-	PRE-TIN	CuNiSi	964201-4	C
-	PRE-TIN	CuFe	964201-3	C
-	PRE-TIN	CuSn	964201-2	C
-	PRE-TIN	CuZn30	964201-1	C
LOOSE PIECE	FINISH	MATERIAL	PART NO.	REV.



WIRE RANGE: 0.5 - 1.0 mm²
INSULATION RANGE: Ø1.4 - 2.3 mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
FINISH

±0.2
±1°
-

DWN
J. Salo
CHK
R. Sole
APVD
L. Batllo
PRODUCT SPEC
APPLICATION SPEC
WEIGHT
CUSTOMER DRAWING

20-AUG-10
25AUG2010
25AUG2010
-
-
-

TE Connectivity

NAME
STANDARD TIMER CONTACT
WITH TWO LOCKING LANCES
-

SIZE
A3

CAGE CODE
-

DRAWING NO
C-964201

RESTRICTED TO
-

SCALE
5:1

SHEET
1 OF 1

REV
C2

1470-19 (3/11)