





MALE END VIEW		FEMALE END VIEW		SPECIFICATIONS																			
				<table><tr><td>HOUSING MATERIAL/COLOR</td><td>NYLON/BLACK</td></tr><tr><td>RECEPTACLE MATERIAL/PLATING</td><td>BRASS/NICKEL</td></tr><tr><td>CONTACT CARRIER MATERIAL</td><td>NYLON</td></tr><tr><td>CONTACT MATERIAL/PLATING</td><td>BRASS/GOLD</td></tr><tr><td>O-RING MATERIAL</td><td>VITON</td></tr><tr><td>OPERATING VOLTAGE [V]</td><td>10–30 VDC</td></tr><tr><td>OPERATING CURRENT [A]</td><td>2.0 AMPS/SIGNAL, 9.0 AMPS TOTAL</td></tr><tr><td>PROTECTION CLASS</td><td>IP67, IP69K – ONLY WHEN ALL RECEPTACLES ARE COVERED WITH PLUGS OR CONNECTED</td></tr><tr><td>OPERATING TEMPERATURE</td><td>–40°C to +85°C (–40°F to +185°F)</td></tr></table>		HOUSING MATERIAL/COLOR	NYLON/BLACK	RECEPTACLE MATERIAL/PLATING	BRASS/NICKEL	CONTACT CARRIER MATERIAL	NYLON	CONTACT MATERIAL/PLATING	BRASS/GOLD	O-RING MATERIAL	VITON	OPERATING VOLTAGE [V]	10–30 VDC	OPERATING CURRENT [A]	2.0 AMPS/SIGNAL, 9.0 AMPS TOTAL	PROTECTION CLASS	IP67, IP69K – ONLY WHEN ALL RECEPTACLES ARE COVERED WITH PLUGS OR CONNECTED	OPERATING TEMPERATURE	–40°C to +85°C (–40°F to +185°F)
HOUSING MATERIAL/COLOR	NYLON/BLACK																						
RECEPTACLE MATERIAL/PLATING	BRASS/NICKEL																						
CONTACT CARRIER MATERIAL	NYLON																						
CONTACT MATERIAL/PLATING	BRASS/GOLD																						
O-RING MATERIAL	VITON																						
OPERATING VOLTAGE [V]	10–30 VDC																						
OPERATING CURRENT [A]	2.0 AMPS/SIGNAL, 9.0 AMPS TOTAL																						
PROTECTION CLASS	IP67, IP69K – ONLY WHEN ALL RECEPTACLES ARE COVERED WITH PLUGS OR CONNECTED																						
OPERATING TEMPERATURE	–40°C to +85°C (–40°F to +185°F)																						
 M23 connector (P1)		 Auto Fast (J1–J4)																					



SOURCE DRAWING - FOR REFERENCE ONLY

<table> <tr> <td>D</td><td>UPDATE PROTECTION CLASS</td><td>RDS</td><td>05/21/14</td><td>45752</td></tr> <tr> <td>REV</td><td>DESCRIPTION</td><td>BY</td><td>DATE</td><td>ECO NO.</td></tr> </table>	D	UPDATE PROTECTION CLASS	RDS	05/21/14	45752	REV	DESCRIPTION	BY	DATE	ECO NO.	RELATED DOCUMENTS 1. 2. 3. 4. MATERIAL SEE SPECIFICATIONS FINISH SEE SPECIFICATIONS	3RD ANGLE PROJECTION  ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY CONTACT TURCK FOR MORE INFORMATION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED. DRFT RDS APVD SWC DATE 11/23/04 SCALE 1=1.5 UNIT OF MEASUREMENT MILLIMETER [INCH] DO NOT SCALE THIS DRAWING	3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com TURCK INC High Technology Sensors and Automation Controls DESCRIPTION 4MB12Z-5P3-CS19 IDENTIFICATION NO. E8026485 REV D FILE: E8026485 SHEET 1 OF 1
D	UPDATE PROTECTION CLASS	RDS	05/21/14	45752										
REV	DESCRIPTION	BY	DATE	ECO NO.										