






SEE DETAIL V- SECTION T-T



60.96 [2.400]	72.64 [2.860]	82.80 [3.260]	78.74 [3.100]	68.58 [2.700]	50	1-111749-0
48.26 [1.900]	59.94 [2.360]	70.10 [2.760]	66.04 [2.600]	55.88 [2.200]	40	111749-9
40.64 [1.600]	52.32 [2.060]	62.48 [2.460]	58.42 [2.300]	48.26 [1.900]	34	111749-8
27.94 [1.100]	39.62 [1.560]	49.78 [1.960]	45.72 [1.800]	35.56 [1.400]	24	111749-5
22.86 [.900]	34.54 [1.360]	44.70 [1.760]	40.64 [1.600]	30.48 [1.200]	20	111749-4
15.24 [.600]	26.92 [1.060]	37.08 [1.460]	33.02 [1.300]	22.86 [.900]	14	111749-2
10.16 [.400]	21.84 [.860]	32.00 [1.260]	27.94 [1.100]	17.78 [.700]	10	111749-1
E	D	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN: 15 MAR 99 C: REISFNYDER		 Tyco Electronics Corporation Haverhill, PA 17105-3608	
DIMENSIONS: mm [INCHES]		DIN: 15 MAR 99 C: REISFNYDER		NAME: _____	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPRO: 15 MAR 99 C: REISFNYDER		PRODUCT SPEC: _____ 108-40018 APPLICATION SPEC: _____	
0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		SIZE: _____ CAGE CODE: _____ DRAWING NO: _____ A1 00779		HEADER ASSEMBLY UNIVERSAL AMP LATCH RESTRICTED TO	
MATERIAL: _____		WEIGHT: _____		SCALE: 4:1 SHEET: 1 OF 1 REV: _____	
 6		 4		CUSTOMER DRAWING	