






SECTION Y-Y

- ① HOUSING MATERIAL: GLASS-FILLED POLYMER.
- ② CONTACT MATERIAL: COPPER ALLOY.
- ③ CONTACT FINISH: DIN 41612 CLASS 2 IN CONTACT AREA.
TIN PLATE ON POSTS.
- ④ PART NUMBER, DATE CODE IDENTIFICATION, CSA LOGO, THIS APPROXIMATE AREA.
- ⑤ CONTACT POINT.
- ⑥ MARKING ON THIS SIDE.
- ⑦ RECOMMENDED HOLE SIZE FOR MANUAL APPLICATION OF CONNECTOR
ONTO PC BOARD.

1 THRU 32	X	X	X	96	5650461-5
1 THRU 32	X	X	X	96	5650461-4
POSITIONS LOADED	C	B	A	NO. OF LOADED POSITION	ASSY PART NUMBER
	ROWS	LOADED			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. NO. POLIGNONE 03JUN05 CHK. A. SHARPE 03JUN05 APD. A. SHARPE 03JUN05		ROWS LOADED POSITION  TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 2 PLC ± - 3 PLC ± 0.13[.005] 4 PLC ± - ANGLES ± -		NAME ASSEMBLY, RECEPTACLE, EUROCARD, TYPE R, LEAD-FREE, 96 POSITION, 2.79[.110] SOLDER POSTS	
		PRODUCT SPEC - APPLICATION SPEC -		SIZE A1 PAGE CODE 00779 DRAWING NO. C-5650461	
MATERIAL 1 2		FINISH 3		WEIGHT - CUSTOMER DRAWING	
				SCALE 4:1 SHEET 1 of 1 REV P	