

PIN Power Inductor RCH-106



Halogen Free



Description

- Ferrite drum core construction.
- Magnetically unshielded.
- L × W × H: 10.5 × 10.5 × 6.5mm Max.
- Product weight: 1.7 g(Ref.)
- Moisture Sensitivity Level: 1
- RoHS compliance.
- Halogen Free available.

Environmental Data

- Operating temperature range: -40°C ~ +100°C (including coil's self temperature rise)
- Storage temperature range: -40°C ~ +100°C


Packaging

- Box packaging.


Applications

- Ideally used in Printers, LCD TV, DVD, Copy Machine, Mainboard of the compounding machines etc. as DC-DC Converter inductors.

Dimension - [mm]



Schematics - [mm]



(100M ~ 102K)

(1R0N ~ 7R8M)

PIN Power Inductor RCH-106




Electrical Characteristics

PART NO	STAMP	INDUCTANCE [WITHIN] ※1	D.C.R. (Ω) [MAX.] (at 20°C)	RATED CURRENT (A) ※2
RCH106NP-1R0N	1R0N	1.0 μ H \pm 30 %	5.0m	9.3
RCH106NP-1R2N	1R2N	1.2 μ H \pm 30 %	6.9m	8.0
RCH106NP-1R8M	1R8M	1.8 μ H \pm 20 %	8.0m	7.4
RCH106NP-2R8M	2R8M	2.8 μ H \pm 20 %	11.8m	6.0
RCH106NP-3R6M	3R6M	3.6 μ H \pm 20 %	13.8m	5.7
RCH106NP-5R1M	5R1M	5.1 μ H \pm 20 %	19.6m	4.6
RCH106NP-6R3M	6R3M	6.3 μ H \pm 20 %	23.1m	4.2
RCH106NP-7R8M	7R8M	7.8 μ H \pm 20 %	24.8m	3.9
RCH106NP-100M	100M	10 μ H \pm 20 %	0.040	3.6
RCH106NP-120M	120M	12 μ H \pm 20 %	0.044	3.3
RCH106NP-150M	150M	15 μ H \pm 20 %	0.058	2.9
RCH106NP-180M	180M	18 μ H \pm 20 %	0.064	2.7
RCH106NP-220M	220M	22 μ H \pm 20 %	0.088	2.4
RCH106NP-270M	270M	27 μ H \pm 20 %	0.10	2.2
RCH106NP-330K	330K	33 μ H \pm 10 %	0.11	2.0
RCH106NP-390K	390K	39 μ H \pm 10 %	0.14	1.8
RCH106NP-470K	470K	47 μ H \pm 10 %	0.16	1.7
RCH106NP-560K	560K	56 μ H \pm 10 %	0.19	1.5
RCH106NP-680K	680K	68 μ H \pm 10 %	0.22	1.4
RCH106NP-820K	820K	82 μ H \pm 10 %	0.29	1.3
RCH106NP-101K	101K	100 μ H \pm 10 %	0.32	1.3
RCH106NP-121K	121K	120 μ H \pm 10 %	0.38	1.2
RCH106NP-151K	151K	150 μ H \pm 10 %	0.50	1.0
RCH106NP-181K	181K	180 μ H \pm 10 %	0.56	0.84
RCH106NP-221K	221K	220 μ H \pm 10 %	0.78	0.76
RCH106NP-271K	271K	270 μ H \pm 10 %	0.92	0.69
RCH106NP-331K	331K	330 μ H \pm 10 %	1.1	0.62
RCH106NP-391K	391K	390 μ H \pm 10 %	1.3	0.57
RCH106NP-471K	471K	470 μ H \pm 10 %	1.5	0.52
RCH106NP-561K	561K	560 μ H \pm 10 %	1.9	0.48
RCH106NP-681K	681K	680 μ H \pm 10 %	2.2	0.43
RCH106NP-821K	821K	820 μ H \pm 10 %	2.6	0.40
RCH106NP-102K	102K	1.0 mH \pm 10 %	3.2	0.36

※1: Inductance measuring condition: 1.0 μ H ~ 7.8 μ H at 7.96MHz
 10 μ H ~ 1.0mH at 1kHz













※2: The rated current indicates the lower value of current when the inductance is 10% lower than its initial value at D.C. superposition or the temperature of coil rises 40°C with D.C. current passing. (Ta=20°C)

PIN Power Inductor RCH-106



Saturation Current & Temperature Rise Graph

— L (20°C) — L (100°C) — ΔT















PIN Power Inductor RCH-106



Saturation Current & Temperature Rise Graph

— L (20°C) — L (100°C) — ΔT












PIN Power Inductor RCH-106



Saturation Current & Temperature Rise Graph

— L (20°C) — L (100°C) — ΔT



Please refer to the sales offices on our website - <http://www.sumida.com>

Hong Kong
Tel.+852-2880-6781
FAX.+852-2565-9600
sales@hk.sumida.com
Saitama(Japan)
Tel.+81-48-691-7300
FAX.+81-48-691-7340
sales@jp.sumida.com
Chicago
Tel.+1-847-545-6700
FAX. +1-847-545-6720
sales@us.sumida.com

Shanghai
Tel.+86-21-5836-3299
FAX.+86-21-5836-3266
shanghai.sales@cn.sumida.com
Seoul
Tel.+82-2-6237-0777
FAX.+82-2-6237-0778
sales@kr.sumida.com
Oberzell
Tel.+49-8591-937-0
FAX. +49-8591-937-103
contact@eu.sumida.com

Shenzhen
Tel.+86-755-8291-0228
FAX.+86-755-8291-0338
shenzhen.sales@cn.sumida.com
Singapore
Tel.+65-6296-3388
FAX.+65-6841-4426
sales@sg.sumida.com
Neumarkt
Tel.+49-9181-4509-110
FAX. +49-9181-4509-310
infocomp@eu.sumida.com

Taipei
Tel.+886-2-8751-2737
FAX.+886-2-8751-2738
sales@tw.sumida.com
San Jose
Tel.+1-408-321-9660
FAX.+1-408-321-9308
sales@us.sumida.com