

**Part Number: 79108-0052**

2.00mm Pitch Milli-Grid™ Flex-to-Board Vertical Receptacle Dual Row Through-Hole, 0.76µm Gold (Au) Selective Plating, 6 Circuits, Tin/Lead

Image not available

|                     |  |
|---------------------|--|
| <b>Status:</b>      | <b>OBsolete</b>                              |
| <b>Replacement:</b> | <a href="#">791081052</a>                    |
| <b>Series:</b>      | <a href="#">79108</a>                        |
| <b>Category:</b>    | FFC/FPC Connectors                           |
| <b>Overview:</b>    | <a href="#">Milli-Grid™ Connector System</a> |

*Series image - Reference only*

**Product Environmental Compliance**

[EU RoHS](#): Not RoHS Compliant

[China RoHS](#):

[REACH SVHC](#):

[Low-Halogen Status](#): Not Reviewed

**Part Detail****General**

|               |  |
|---------------|--|
| <b>Status</b> | <b>Obsolete</b>                              |
| Category      | FFC/FPC Connectors                           |
| Series        | <a href="#">79108</a>                        |
| Obsolete Date | 2005/06/01                                   |
| Overview      | <a href="#">Milli-Grid™ Connector System</a> |
| Product Name  | Milli-Grid™                                  |

**Physical**

|                                |                 |
|--------------------------------|-----------------|
| Circuits (Loaded)              | 6               |
| Contact Position               | Top             |
| Durability (mating cycles max) | 50              |
| Entry Angle                    | 90° Angle       |
| Number of Rows                 | 2               |
| Orientation                    | Right Angle     |
| PC Tail Length                 | 1.27mm          |
| PCB Locator                    | No              |
| PCB Retention                  | None            |
| PCB Thickness - Recommended    | 0.60mm          |
| Packaging Type                 | Tube            |
| Pitch - Mating Interface       | 2.00mm          |
| Polarized to PCB               | No              |
| Stackable                      | No              |
| Surface Mount Compatible (SMC) | No              |
| Temperature Range - Operating  | -55°C to +105°C |
| Termination Interface: Style   | Through Hole    |
| Wire/Cable Type                | FFC/FPC         |

**Electrical**

(Please review the Product Specification for specific details.)

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 1A   |
| Voltage - Maximum             | 125V |

**Solder Process Data**

|  |            |
|--|------------|
| Replacement RoHS Compliant Part Number | 0791081052 |
|--|------------|

**Material Info****Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application Tooling**

[Check our list of old tooling that used to be available for this part](#)

