


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	08/15/01	MCCORMICK
B	PRODUCT VALIDATION UPDATES (ECN 1204)	12/10/02	MCCORMICK
C	ECN3022: UPDATED DRAWING FORMAT. CN RELEASE	09/27/07	D.PARHAM



NOTES:

1. CABLE SHALL BE TESTED FOR CONTINUITY.
2. CABLE SHALL BE ROHS COMPLIANT.
3. CABLE SHALL BE INDIVIDUALLY PACKAGED IN A POLY BAG.

DIMENSIONS ARE IN INCHES (mm)
UNLESS OTHERWISE SPECIFIED,
TOLERANCES TO BE:
.X ± .1 (.25) ANGLES ± 2°
.XX ± .01 (.25)
.XXX ± .005 (.13)
OVERALL CABLE LENGTH TOL:
≤ 60 (1524) +3 (76.2) / -0
> 60 (1524) +5% / -0%



APPROVALS	DATE
DRAWN BY MCCORMICK	05/03/01
CHECKED BY D.PARHAM	06/06/01
APPROVED BY ENG	08/15/01

CONFIGURATION DETAILS OF
UNDIMENSIONED FEATURES
MAY VARY

L-com CONNECTIVITY PRODUCTS		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY		COAXIAL	
PRODUCT DESCRIPTION		CA BNC M/BNC M RG59A/U	
SIZE A	FSCM NO. 43321	DWG. NO. CC59A	REV. C
SCALE: NONE		CAD FILE: CC59A.SLDDRW	
		SHEET 1 OF 1	