











RECOMMENDED MODULE LAYOUT



TYPE "R"	3.3 VOLT.
TYPE "L"	2.5 VOLT.
TYPE "C"	1.8 VOLT.
CENTER KEY	DESCRIPTION

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		A FCI www.fciconnect.com					
ltr	ecn no	dr	date	linear	.X ± 0.38/.015			projection 	title DDR 184P .050" 1-ROW, V/T ASS'Y METAL CLIP(FOR DELL)					
A					.XX ± 0.25/.010									
					.XXX ± 0.15/.005									
				angles	0° ±2°			MM scale 1.5:1	product family size A4	DDR		code		
				dr	Desmond Hu	10/16/03	dwg no			10035612	sheet 2 of			
				engr	Desmond Hu	10/16/03								
				chr	Desmond Hu	10/16/03								
				appd	Joseph Hsia	10/16/03								
sheet index	revision sheet													



DDR ASSEMBLY PART NUMBER
10035612 - ☐ ☐ ☐ ☐

RECOMMENDED CIRCUIT BOARD HOLE LAYOUT

STYLE

- 1 : FOR 3.3 VOLT.
- 2 : FOR 2.5 VOLT.
- 3 : FOR 1.8 VOLT.

METAL CLIP

1 : WITH METAL CLIP + DIM."D"=4.00/.157.

PLATING

CODE	CONTACT	SOLDERTAIL	UNDERPLATE	CODE	CONTACT	SOLDERTAIL	UNDERPLATE
2	15μ"(0.38μm) MIN. GOLD	100μ"(2.54μm) MIN. TIN/LEAD	50μ"(1.27μm) MIN. NICKEL OVERALL	7LF	15μ"(0.38μm) MIN. GOLD	100μ"(2.54μm) MIN. 100%TIN	50μ"(1.27μm) MIN. NICKEL OVERALL
3	30μ"(0.76μm) MIN. GOLD			8LF	30μ"(0.76μm) MIN. GOLD		
4	GOLD FLASH			9LF	GOLD FLASH		

TAIL LENGTH

CODE	DIM. "B"	DIM. "C"
0	2.59 .102	2.44 .096
1	3.35 .132	3.20 .126

COLOR OF HOUSING AND EJECTOR

- 0 : BLACK HOUSING + IVORY EJECTOR
- 3 : BLACK HOUSING + BLACK EJECTOR

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		FCI www.fciconnect.com		
ltr	ecn no	dr	date	linear	.X ± 0.38/.015	projection	title	DDR 184P .050" 1-ROW, V/T ASS'Y METAL CLIP(FOR DELL)		
D					.XX ± 0.25/.010					
					.XXX ± 0.15/.005					
				angles	0° ±2°	MM	product family	DDR		
				dr	Desmond Hu			10/16/03	size	dwg no
				engr	Desmond Hu			10/16/03		
				chr	Desmond Hu	10/16/03	scale	A4		
				appd	Joseph Hsia	10/16/03			1.5:1	10035612
sheet index	revision sheet									