

Distributed by:

JAMECO[®]
ELECTRONICS


www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 37331

PART NO.	CA-XXP-XXX-XX
----------	---------------

REVISIONS					
LTR	DESCRIPTION		DATE	APPROVE	
A	INITIAL RELEASE	SEE DO 4547	C.P.	7-5-01	A.J
B	SEE DO	4616	C.P.	9-10-01	A.J
C	SEE DO	4630	C.P.	9-25-01	A.J
D	SEE DO	5580	C.P.	8-26-04	A.J
E	SEE DO	6130	C.P.	6-27-06	A.J
F	SEE DO	6279	C.P.	11-17-06	A.J



CA-XXP-XXX-XX

NO. OF POS.

PLUG STANDARD, FORK

PLATING

BLANK = TAIL AREA : .000010 [.00025] GOLD
FORK AREA : .000150 ±.000025 [.00381±.00064] TIN
UNDERPLATE : .000075 [.00190] NICKEL

T = .000150 ±.000025 [.00381±.00064] TIN
OVER .000075 [.00190] NICKEL

CONTACT STYLE

TAIL LENGTH	FORK HEIGHT
02 = .190 [4.83]	.060 [1.52]
04 = .150 [3.81]	.060 [1.52]
11 = .190 [4.83]	.100 [2.54]
12 = .150 [3.81]	.100 [2.54]

CONFIGURATION (Add if required)

BLANK = STANDARD WIDTH
NW = NARROW WIDTH

SPECIFICATIONS :

ENVIRONMENTAL :

TEMPERATURE RANGE : -65°C TO +125°C

MECHANICAL :

INSULATOR MATERIAL :	GLASS FILLED NYLON, BLACK, UL94V-0
CONTACT MATERIAL :	BRASS, CDA 260

ELECTRICAL :

CURRENT RATING : 1 AMP
VOLTAGE RATING : 300 Vrms
DIELECTRIC WITHSTANDING VOLTAGE : 500 Vrms MIN.
INSULATION RESISTANCE : > 5000 Megohms

TABULATION :

NO. OF POS	DIM 'A'		DIM 'B'		DIM 'C'		DIM 'D'		DIM 'E'	
	IN	MM	IN	MM	IN	MM	IN	MM	IN	MM
08	.450	[11.43]	.300	[7.62]	.300	[7.62]	.470	[11.94]	.034	[0.86]
14	.750	[19.05]	.600	[15.24]	.300	[7.62]	.470	[11.94]	.034	[0.86]
14-NW	.750	[19.05]	.600	[15.24]	.300	[7.62]	.395	[10.03]	.024	[0.61]
16	.850	[21.59]	.700	[17.78]	.300	[7.62]	.470	[11.94]	.034	[0.86]
16-NW	.850	[21.59]	.700	[17.78]	.300	[7.62]	.395	[10.03]	.024	[0.61]
18	.950	[24.13]	.800	[20.32]	.300	[7.62]	.470	[11.94]	.034	[0.86]
20	1.050	[26.67]	.900	[22.86]	.300	[7.62]	.470	[11.94]	.034	[0.86]
24	1.250	[31.75]	1.100	[27.94]	.600	[15.24]	.795	[20.19]	.034	[0.86]
28	1.450	[36.83]	1.300	[33.02]	.600	[15.24]	.795	[20.19]	.034	[0.86]
40	2.050	[52.07]	1.900	[48.26]	.600	[15.24]	.795	[20.19]	.034	[0.86]

DIMENSIONS ARE IN INCHES TOLERANCES ARE:		APPROVALS DRAWN CUONG_P 6/29/01		 CIRCUIT ASSEMBLY CORP. 18 THOMAS ST., IRVINE, CALIFORNIA 92618-2777	
DECIMALS ANGLES .XX ± .010 ± 3° .XXX .005		CHECKED A.JOCHEN 7/05/01		DIP PLUG STANDARD, FORK STYLE SERIES 'P' "ROHS COMPLIANT"	
DIMENSIONS IN BRACKETS [X.X] ARE IN MILLIMETERS TOLERANCES ARE:		THE INFORMATION AND DESIGN DISCLOSED HEREIN WAS ORIGINATED BY AND IS THE PROPERTY OF CIRCUIT ASSEMBLY CORPORATION. CIRCUIT ASSEMBLY CORPORATION RESERVES ALL PATENT, COPYRIGHT, AND MANUFACTURING, REPRODUCTION, AND SALES RIGHTS THERE TO, AND TO ANY ARTICLE DISCLOSED HEREIN EXCEPT TO THE EXTENT RIGHTS ARE EXPRESSLY GRANTED TO OTHERS. THE FOREGOING DOES NOT APPLY TO PROPRIETARY RIGHTS.		SIZE CODE IDENT NO. DRAWING NO. REV. C 52072 620394 F	
DECIMALS ANGLES .XX ± .05 ± 3° .XXX ± .1		DO NOT SCALE DRAWING		SCALE: 4:1 SHEET 1 OF 1	