



REV	ECN	APPD
—	4785	

L=PITCH X POSITIONS

NOTES:

- 1 PARTS GREATER THAN 3 POSITIONS ASSEMBLED WITH APPROPRIATE COMBINATIONS OF 2 AND 3 POSITION MODULES. (3 POSITION MODULE SHOWN)

- 2 .197 [5mm] PITCH DIMENSIONS INDICATED IN PARENTHESES.



RATINGS

CURRENT – 13.5A
VOLTAGE – 300V
U.L. FILE NO.



RATINGS

CURRENT – 13.5A
VOLTAGE – 300V
CSA FILE NO.

ESLTXXX20

- 1 NUMBER OF POSITIONS

- 2 PITCH:
1=.197[5MM]
2=.2005.08MM]


INSTALLATION RECOMMENDATIONS

WIRE RANGE: 14–30 AWG
WIRE STRIP LENGTH: .197–.236
TIGHTENING TORQUE: 4.4 LB-IN.

MATERIALS

HOUSING: POLYAMIDE 6/6, COLOR: BLACK
CONTACT: COPPER ALLOY, TIN PLATED
SCREW / CAGE CLAMP: COPPER ALLOY, NICKEL PLATED

OPERATING TEMPERATURE RANGE: –40°C TO 110°C
RECOMMENDED PCB THICKNESS: .094" MAX



DIN VDE 0627:1986
DIN VDE 0110–1:1989
EN 60947–1:1991
EN 60947–7–1:1992

CURRENT – 13.5A
VOLTAGE – 250V
TUV FILE NO.


DIMENSIONS

ANSI Y14.5M
UNITS: INCHES
ACAD FILE

TOLERANCES

.XX ±.01
.XXX ±.005
ANGLES ±2°

PROJECTION



SPECIFICATION DRAWING

ENGR
B. JAWORSKI 11/1/01

CHKD

APPD



TITLE

ESLT TERMINAL BLOCK
LOW PROFILE, MID TOWER
.200/.197 PITCH

SIZE

A

DWG NO.

ESLT02120

REV

—

CODE: 58982

SCALE: NONE

SHEET 1 OF 1

ORIGINAL
STAMPED
IN RED

THIS DOCUMENT CONTAINS
PROPRIETARY INFORMATION WHICH
IS THE CONFIDENTIAL PROPERTY
OF PCD, INC. PEABODY, MA, USA