

Abbr.	TOLERANCE	
	P=0.5	P=1.0
P	±0.05	±0.08
Pt	±0.08	±0.10
W	±0.08	±0.10
M	±0.08	±0.12
Cw	±0.02	±0.03
L	(30~100)±3, (101~300)±5, (301~600)±10, (Length more than 601mm)±15mm	

RoHS Compliant			
I	05-AUG-15	TEMPERATURE	AK
H	21-JAN-13	CT DIM	QL
REV	DATE	FILE	BY



MATERIAL
INSULATOR MATERIAL: PET (WHITE)
SUPPORT TAPE: PET (BLUE)
CONTACT MATERIAL: COPPER
CONTACT PLATING: TIN
QUALITY CLASS: 20 MATING CYCLES MIN.
PITCH: 1.00 MM

ENVIRONMENTAL
OPERATING TEMPERATURE: -30°C UP TO 105°C
HEAT RESISTANCE: 110°C x 96 HRS
FLAMMABILITY RATING UL SUB.758
MOISTURE RESISTANCE: 40°C, 95% RH x 96 HRS
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
CURRENT RATING: 1.0 A MAX
WORKING VOLTAGE: 60V
INSULATION RESISTANCE: >1000 MOHM/M (500 VDC)
DIELECTRIC STRENGHT: 500 VAC/MN NO BREAKDOWN
CONDUCTOR RESISTANCE: <1.09 OHM/M
CONTACT RESITANCE: <20 MOHMS



STANDARD
 CERTIFIED: E328849

MECHANICAL
ELONGATION OF INSULATOR: > 60 %
TENSIL STRENGTH OF INSULATION: >3.5KG/MM²
FLEXING TEST: 180° >20 TIMES
ABRASION: >10000 TIMES
PULL/OUT: >20 TIMES

PACKAGING
BAG

DIMENSION & TOLERANCE
 $W = (N+1) \times P$
 $Pt = (N-1) \times P$

No. of PIN	Dimension												
	P	Pt	L	W	M	Cw	Ct±0.01	S1±1.0	S2±1.0	d1±2.0	d2±2.0	Ft±0.01	St±0.01
XX *****	1.0	(XX - 1) x P	LLL *****	(XX + 1) x P	1.0	0.70	0.035	5.0	5.0	10.0	10.0	0.043	0.225

PROJECTION: 	GENERAL TOLERANCE $.X = +/_{0.2}$ $.XX = +/_{0.15}$		
APPROVAL: Gm0	UNIT: MM SCALE: SHEET: 1/2 DRAW: CH	DESCRIPTION: 1.00MM FLAT FLEXIBLE CABLE TYPE 1 XX NB OF PIN: [REDACTED] / LLL OVERALL LENGTH: [REDACTED] MM WERI PART NO: 686 [REDACTED] 001 XX LLL	SIZE A4

