

## TCT50-06E07K

### Description:

Triad control transformers come with tamper resistant shrouds for safety and a steel bracket welded to the bottom of the transformer for ease of mounting. These transformers are design and have the safety agency recognition for application where a Class 2 transformer is necessary. Some of the applications would include, but not limited to HVAC, Control boards, Lighting, etc.

### Electrical Specifications (@25C):

1. Maximum Power: 50VA
2. \*Input (BLK-WHT): 120V, 50/60 Hz, (Fuse: 0.800A Max)  
(BLK-RED): 240V, 50/60Hz, (Fuse: 0.400A Max)
3. Output (YEL-YEL): 24V @ 2.08Amps, (Fuse: 3.0A Max)
4. Voltage Regulation: 15% TYP @ full load to no load
5. Temperature Rise: <40°C TYP
6. Hipot: 1500VAC – Input to Output, Input & Output to Core
7. Recommended Fusing: UL Listed, 3AG time-delay type. Fuse can be use on primary or secondary.

\* Only one input voltage to be applied to primary at any time.

### Construction:

Three flange bobbin construction with primaries and secondaries wound side by side for low capacitive coupling. Unit weight is 2.0lbs.

### Agency File:


UL: File E65390, UL 5085-3 (1585), Class 2 Transformer  
cUL: File E65390, UL 5085-3 (1585) For Canadian Use (CSA 22.2, No.66.3-06)



### Connections:

Input:  $12\pm1"$  insulated leads, stripped and tinned  $0.20\pm0.08"$ , 18AWG stranded  
Output:  $12\pm1"$  insulated leads, stripped and tinned  $0.20\pm0.08"$ , 18AWG stranded

### Schematic:



**RoHS Compliance:** As of manufacturing date February 2005, all standard products meet the requirements of 2011/65/EU, known as the RoHS initiative.

As of April 7, 2008, UL standards 506 and 1585 will be migrated to UL 5085-2 and 5085-3, respectively.

\* Upon printing, this document is considered "uncontrolled". Please contact Triad Magnetics' website for the most current version.



Picture for illustration only!!

