




File: E209153



Mechanical Specifications (mm)

D:	31.0	± max
T:	6.0	± max
Lead Diameter	1.0	± nom
S:	7.8	± nom
L:	38.0	± nom
Coating Lead Run Down (straight Leads)	4.0	± max
B:	7.80	± nom
C:	3.82	± nom



Electrical Specifications

Resistance:	5.0	Ω	± 20 %
Max Steady State Current upto 65°C:	20.00	A	
Max Rec. Energy Rating:	200	J	
Maximum Capacitance @ 120 VAC:	13,893	µf	
Maximum Capacitance @ 240 VAC:	3,473	µf	
Resistance @ 100% Max Current:	0.00	Ω	
Resistance @ 50% Max Current:	0.08	Ω	
Body Temperature at 100% Max Current:	206.00	°C	
Dissipation Constant:	45.4	mw/°C	
Thermal Time Constant:	194	Sec.	
Material Type (for Beta and Curve):	H		

SL32 5R020

Date: 01/12/2016

Drawn by: Erin Landis

Ametherm, Inc.
961 Fairview Drive
Carson City, Nevada USA 89701
www.ametherm.com

Approved By: Chad Terry

Revision: B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ametherm:](#)

[SL325R020B](#)

[Vishay:](#)

[SL32 5R020](#)