


features

- Surface mount
- Operating temperature: -40°C ~ +125°C
- Flat top suitable for high speed pick-and-place components
- Excellent high frequency applications
- High Q factors and self-resonant frequency values
- Marking: White body color with no marking (0402)
Black body color with white marking (0603, 0805, 1008)
- Products with lead-free terminations meet EU RoHS requirements
- AEC-Q200 Qualified

dimensions and construction



Size Code	Dimensions inches (mm)					
	L	W1	W2	t	h	d
KQT0402	.039±.004 (1.0±0.1)	.02±.004 (0.5±0.1)	.02±.004 (0.5±0.1)	.022±.004 (0.55±0.1)	.006±.004 (0.15±0.1)	.01±.004 (0.25±0.1)
KQ0603	.063±.004 (1.6±0.1)	.039±.004 (1.0±0.1)	.033±.004 (0.85±0.1)	.035±.004 (0.9±0.1)	.01±.006 (0.25±0.15)	.014±.004 (0.35±0.1)
KQ0805	.079±.008 (2.0±0.2)	.059±.008 (1.5±0.2) (3.3nH-390nH)	.053±.004 (1.35±0.1)	.051±.008 (1.3±0.2)	.016±.006 (0.40±0.15)	.018±.004 (0.45±0.1)
		.063±.008 (1.6±0.2) (470nH-820nH)				
KQ1008	.098±.008 (2.5±0.2)	.087±.008 (2.2±0.2)	.079±.004 (2.0±0.1)	.071 ^{+.008} ₋₀ (1.8 ^{+.02} ₋₀)	.018±.006 (0.45±0.15)	.018±.004 (0.45±0.1)

ordering information

New Part #	KQ	1008	T	TE	10N	J
Type	KQ KQT	Size Code 0402 0603 0805 1008	Termination Material T: Sn	Packaging TP: 2mm pitch paper (0402: 10,000 pieces/reel) TD: 7" paper tape (0402: 2,000 pieces/reel) TE: 7" embossed plastic (0603, 0805, 1008: 2,000 pieces/reel)	Nominal Inductance 3 digits: 10N: 10nH R10: 0.1μH 1R0: 1.0μH	Tolerance B: ±0.1nH C: ±0.2nH G: ±2% H: ±3% J: ±5% K: ±10% M: ±20%

For further information on packaging, please refer to Appendix A.

applications and ratings

Part Designation	Marking	Nominal Inductance (nH)	L Measuring Frequency (MHz)	Inductance Tolerance	Q Quality Factor Minimum	Q Measuring Frequency (MHz)	Self Resonant Frequency Minimum (MHz)	DC Resistance Maximum (Ω)	Allowable DC Current Maximum (mA)	
KQT0402T**1N0*	—	1.0	250	B: ±0.1nH C: ±0.2nH	16	250	11000	0.045	1360	
KQT0402T**1N9*		1.9			19		9600	0.070	1040	
KQT0402T**2N0*		2.0								
KQT0402T**2N2*		2.2								
KQT0402T**2N4*		2.4			18		8000	0.068	960	
KQT0402T**2N7*		2.7			17			0.120	700	
KQT0402T**3N3*		3.3		H: ±3% J: ±5% K: ±10%	19		7200	0.066	840	
KQT0402T**3N6*		3.6			18		6000	0.091	800	
KQT0402T**3N9*		3.9								
KQT0402T**4N3*		4.3			20		5800	0.083	760	
KQT0402T**4N7*		4.7								
KQT0402T**5N1*		5.1					4800	0.086	680	
KQT0402T**5N6*		5.6			22					
KQT0402T**6N2*		6.2			5800		0.104	680		
KQT0402T**6N8*		6.8			4400					
KQT0402T**7N5*		7.5			20		4200	0.150	650	
KQT0402T**8N2*		8.2					4160	0.104	680	
KQT0402T**8N7*		8.7			20		4000	0.150	650	
KQT0402T**9N0*		9.0			22		3900	0.195	480	
KQT0402T**9N5*		9.5			24		3680	0.120	640	
KQT0402T**10N*		10					3600			
KQT0402T**11N*		11					3450	0.180	560	
KQT0402T**12N*		12			25		3280	0.172		
KQT0402T**13N*		13					3100	0.200	500	
KQT0402T**15N*		15						0.230		
KQT0402T**16N*		16			24		3040	0.202	480	
KQT0402T**18N*		18					3000	0.250	450	
KQT0402T**19N*		19			25		2800	0.323	400	
KQT0402T**20N*		20					2720	0.214		
KQT0402T**22N*		22					2700	0.322		
KQT0402T**23N*		23			24		2480	0.298		
KQT0402T**24N*		24					2400	0.354		
KQT0402T**27N*		27						0.393		
KQT0402T**30N*		30			24		2320	0.550	340	
KQT0402T**33N*		33						0.560	320	
KQT0402T**34N*		34			25		2300	0.550	300	
KQT0402T**36N*		36					2240	0.620	320	
KQT0402T**39N*		39					2200	0.810	300	
KQT0402T**40N*		40			20		2100	0.830	150	
KQT0402T**43N*		43						0.835	240	
KQT0402T**47N*		47			25		2800	1.170	200	
KQT0402T**51N*		51					2000	1.120		
KQT0402T**56N*		56			22		1800	1.810	140	
KQT0402T**68N*		68					1600	2.090	130	
KQT0402T**82N*		82					1500	2.320	120	
KQT0402T**R10*		100								
KQT0402T**R12*		120								

* Add tolerancing character (B, C, G, H, J, K, M)

** Add packaging code

For complete environmental specifications, please refer to www.koaspeer.com

Specifications given herein may be changed at any time without prior notice. Please confirm technical specifications before you order and/or use.

12/01/14

applications and ratings (continued)

Part Designation	Marking	Nominal Inductance (nH)	L Measuring Frequency (MHz)	Inductance Tolerance	Q Quality Factor Minimum	Q Measuring Frequency (MHz)	Self Resonant Frequency Minimum (MHz)	DC Resistance Maximum (Ω)	Allowable DC Current Maximum (mA)	
KQ0603TTE1N6*	C	1.6	250	J: ±5% K: ±10%	24	250	12500	0.03	700	
KQ0603TTE1N8*	0	1.8			16			0.045		
KQ0603TTE3N3*	X	3.3			22		6900	0.055		
KQ0603TTE3N6*	E	3.6						0.063		
KQ0603TTE3N9*	1	3.9						0.08		
KQ0603TTE4N3*	F	4.3					5900	0.063		
KQ0603TTE4N7*	G	4.7			20		5800	0.116		
KQ0603TTE5N1*	Y	5.1			27			0.115		
KQ0603TTE6N8*	2	6.8			4800		0.11			
KQ0603TTE7N5*	H	7.5					28			0.106
KQ0603TTE8N2*	A	8.2		G: ±2% J: ±5% K: ±10%			4600	0.12		
KQ0603TTE8N7*	J	8.7					4800	0.109		
KQ0603TTE9N5*	B	9.5		31			4800	0.125		
KQ0603TTE10N*	3	10						0.13		
KQ0603TTE11N*	K	11		33	4000		0.086			
KQ0603TTE12N*	4	12		35			0.13			
KQ0603TTE15N*	5	15		3300	0.17					
KQ0603TTE16N*	L	16			34		0.104			
KQ0603TTE18N*	6	18		35	3100		0.17			
KQ0603TTE22N*	7	22		38	3000		0.19			
KQ0603TTE23N*	S	23		37			2700	0.15		
KQ0603TTE24N*	M	24					2650	0.135		
KQ0603TTE27N*	8	27	40	200	2800	0.22	600			
KQ0603TTE30N*	N	30	37		2250	0.144				
KQ0603TTE33N*	9	33	40		2300	0.22				
KQ0603TTE36N*	P	36	38		2080	0.25				
KQ0603TTE39N*	0	39	40		2200					
KQ0603TTE43N*	Q	43	39		2000	0.28				
KQ0603TTE47N*	1	47	38		1900	0.30				
KQ0603TTE51N*	T	51				0.31				
KQ0603TTE56N*	2	56	37		1700	0.34				
KQ0603TTE72N*	4	72				0.49				
KQ0603TTE82N*	5	82	150	150	1400	0.54	400			
KQ0603TTER10*	6	100			1350	0.58				
KQ0603TTER11*	7	110			32		1300	0.61	300	
KQ0603TTER12*	8	120					1400	0.65		
KQ0603TTER15*	9	150					1300	1.4		
KQ0603TTER18*	0	180					1300	2.2		
KQ0603TTER20*	U	200	100	100	1200	2.3	140			
KQ0603TTER21*	V	210				2.5	120			
KQ0603TTER22*	1	220			1000	2.4				
KQ0603TTER25*	W	250			24		900	2.3	170	
KQ0603TTER27*	2	270					840	3.17	110	
KQ0603TTER30*	X	300					800	3.0	100	
KQ0603TTER33*	3	330						700	3.7	80
KQ0603TTER39*	4	390			30	50	640	1.21	190	
KQ0603TTER47*	5	470					610	1.26	170	
KQ0603TTER51*	V	510					560	2.09	130	
KQ0603TTER56*	6	560	590	1.89			150			
KQ0603TTER62*	W	620								

* Add tolerance character (B, C, G, H, J, K, M) For complete environmental specifications, please refer to www.koaspeer.com

Specifications given herein may be changed at any time without prior notice. Please confirm technical specifications before you order and/or use.

12/01/14

applications and ratings (continued)

	Part Designation	Marking	Nominal Inductance (nH)	L Measuring Frequency (MHz)	Inductance Tolerance	Q Quality Factor Minimum	Q Measuring Frequency (MHz)	Self Resonant Frequency Minimum (MHz)	DC Resistance Maximum (Ω)	Allowable DC Current Maximum (mA)	
NEW	KQ0603TTER68*	7	680	50	J: ±5% K: ±10%	30	50	540	1.97	140	
	KQ0603TTER72*	C	720					530	2.04	130	
	KQ0603TTER75*	X	750					490	3.09	110	
KQ0603TTER82*	8	820	480					2.95	120		
KQ0603TTER91*	Y	910	440					5.13	90		
KQ0603TTE1R0*	9	1000	400					5.45	80		
KQ0603TTE1R2*	0	1200									
	KQ0805TTE3N3*	0	3.3	250	G: ±2% J: ±5% K: ±10%	50	1500	6000	0.08	600	
	KQ0805TTE6N8*	1	6.8				1000	5500	0.11		
	KQ0805TTE8N2*	2	8.2				4700	0.12			
	KQ0805TTE12N*	3	12			500	4000	0.15			
	KQ0805TTE15N*	4	15				3400	0.17			
	KQ0805TTE18N*	5	18				3300	0.20			
	KQ0805TTE20N*	Y	20	55		500	2600	0.22	500		
	KQ0805TTE22N*	6	22				2500	0.25			
	KQ0805TTE27N*	7	27				2050	0.27			
	KQ0805TTE33N*	8	33	60			2000	0.29			
	KQ0805TTE39N*	9	39				1650	0.34			
	KQ0805TTE43N*	4	43				65	250		1550	0.34
	KQ0805TTE47N*	0	47	1450	0.38						
	KQ0805TTE56N*	1	56	1300	0.42						
	KQ0805TTE68N*	2	68	1200	0.46						
	KQ0805TTE82N*	3	82	50	1100	920	0.56		400		
	KQ0805TTER10*	4	100			250	870			0.64	
	KQ0805TTER12*	5	120				48	850		0.70	
	KQ0805TTER15*	6	150					650		1.0	
	KQ0805TTER16*	H	160							600	1.4
	KQ0805TTER17*	J	170							560	1.5
	KQ0805TTER18*	7	180	23	50		375		1.76	250	
	KQ0805TTER19*	D	190			340	1.9	230			
	KQ0805TTER20*	E	200			188	2.2	190			
	KQ0805TTER21*	F	210			215	2.35	180			
	KQ0805TTER22*	8	220	100	J: ±5% K: ±10%	33	100	4100	0.08	1000	
	KQ0805TTER23*	K	230					3300	0.09		
KQ0805TTER24*	L	240	3000					0.10			
KQ0805TTER25*	G	250	2500					0.11			
KQ0805TTER27*	9	270	55			350	2400	0.12			
KQ0805TTER33*	0	330					1600	0.13			
KQ0805TTER39*	1	390					1600	0.14			
KQ0805TTER47*	2	470					1500	0.15			
KQ1008TTE10N*	10N	10	50	J: ±5% K: ±10% M: ±20%	50	500		0.16			
KQ1008TTE12N*	12N	12									
KQ1008TTE15N*	15N	15									
KQ1008TTE18N*	18N	18									
KQ1008TTE22N*	22N	22			60	350					
KQ1008TTE27N*	27N	27									
KQ1008TTE33N*	33N	33									
KQ1008TTE39N*	39N	39									
KQ1008TTE47N*	47N	47									

* Add tolerance character (C, G, H, J, K, M) For complete environmental specifications, please refer to www.koaspeer.com

Specifications given herein may be changed at any time without prior notice. Please confirm technical specifications before you order and/or use.

12/01/14

applications and ratings (continued)

Part Designation	Marking	Nominal Inductance (nH)	L Measuring Frequency (MHz)	Inductance Tolerance	Q Quality Factor Minimum	Q Measuring Frequency (MHz)	Self Resonant Frequency Minimum (MHz)	DC Resistance Maximum (Ω)	Allowable DC Current Maximum (mA)		
KQ1008TTE56N*	56N	56	50	G: ±2% J: ±5% K: ±10%	65	350	1300	0.18	1000		
KQ1008TTE68N*	68N	68			60		1000	0.20			
KQ1008TTE82N*	82N	82						0.22			
KQ1008TTER10*	R10	100	25		45	100	1000	0.56	650		
KQ1008TTER12*	R12	120					950	0.63			
KQ1008TTER15*	R15	150					850	0.70		580	
KQ1008TTER18*	R18	180					750	0.77	620		
KQ1008TTER22*	R22	220					700	0.84	500		
KQ1008TTER27*	R27	270					600	0.91	500		
KQ1008TTER33*	R33	330					570	1.05	450		
KQ1008TTER39*	R39	390					500	1.12	470		
KQ1008TTER47*	R47	470					450	1.19			
KQ1008TTER56*	R56	560					415	1.33	400		
KQ1008TTER62*	R62	620					375	1.40	300		
KQ1008TTER68*	R68	680						1.47	400		
KQ1008TTER75*	R75	750					360	1.54	360		
KQ1008TTER82*	R82	820					350	1.61	400		
KQ1008TTER91*	R91	910					35		50	320	1.68
KQ1008TTE1R0*	1R0	1000			290	1.75				370	
KQ1008TTE1R2*	1R2	1200			250	1.6				310	
KQ1008TTE1R5*	1R5	1500			28		50	200	1.7	300	
KQ1008TTE1R8*	1R8	1800	160					1.9	270		
KQ1008TTE2R2*	2R2	2200						2.2	250		
KQ1008TTE2R7*	2R7	2700	22		25	140	2.3	230			
KQ1008TTE3R3*	3R3	3300				110	2.7				
KQ1008TTE3R9*	3R9	3900				20	25	100	2.8		
KQ1008TTE4R7*	4R7	4700	90		3.1			210			
KQ1008TTE5R6*	5R6	5600	15		7.9			80	2.5	240	
KQ1008TTE6R8*	6R8	6800				70	2.8	200			
KQ1008TTE8R2*	8R2	8200				65	3.0	170			
KQ1008TTE100*	100	10000				60	3.4	150			

* Add tolerance character (C, G, H, J, K, M)

Operating Temperature Range: -40°C ~ +125°C

The operating temperature range of the coil (ambient temperature + self heating) must remain at +125°C or less

environmental applications

Performance Characteristics

Parameter	Requirements Maximum Limit	Δ L/L Δ Q/Q Typical	Test Method
Resistance to Soldering Heat	No significant abnormality in appearance Δ L/L: ±5%, Δ Q/Q: ±10%	Δ L/L: ±2.7% Δ Q/Q: ±6.6%	260°C ± 5°C, 10s ± 1s
Rapid Change of Temperature	No significant abnormality in appearance Δ L/L: ±5%, Δ Q/Q: ±10%	Δ L/L: ±2.1% Δ Q/Q: ±5.3%	-40°C (30min.)/ +125°C (30min.) 100 cycles
Low Temperature Exposure	No significant abnormality in appearance Δ L/L: ±5%, Δ Q/Q: ±10%	Δ L/L: ±1.8% Δ Q/Q: ±2.8%	-40°C ± 2°C, 1000h
High Temperature Exposure	No significant abnormality in appearance Δ L/L: ±5%, Δ Q/Q: ±10%	Δ L/L: ±1.8% Δ Q/Q: ±5.3%	125°C ± 2°C, 1000h
Moisture Exposure	No significant abnormality in appearance Δ L/L: ±5%, Δ Q/Q: ±10%	Δ L/L: ±0.9% Δ Q/Q: ±6.9%	40°C ± 2°C, 90%~95%RH, 1000h
Resistance to Solvent	No damage and marking shall remain legible	—	Accordance with MIL-STD 202F Method 215

For complete environmental specifications, please refer to www.koaspeer.com

Specifications given herein may be changed at any time without prior notice. Please confirm technical specifications before you order and/or use.

12/01/14

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KOA Speer:

[KQT0402TTD36NJ](#) [KQ0603TTE6N8G](#) [KQ1008TTE15NJ](#) [KQT0402TTD3N6J](#) [KQ1008TTE27NJ](#) [KQT0402TTD3N9J](#)
[KQ1008TTER47G](#) [KQT0402TTD3N3J](#) [KQ1008TTER82G](#) [KQ1008TTER68G](#) [KQ0603TTE7N5G](#) [KQ1008TTER62G](#)
[KQ0603TTE72NG](#) [KQ1008TTER22G](#) [KQ0603TTE68NG](#) [KQ1008TTER27G](#) [KQ1008TTE2R2G](#) [KQ1008TTER15G](#)
[KQ1008TTE22NJ](#) [KQ1008TTER12G](#) [KQ1008TTER18G](#) [KQ1008TTER10G](#) [KQ1008TTE2R7G](#) [KQ1008TTE10NJ](#)
[KQ1008TTE100G](#) [KQ1008TTER91G](#) [KQ1008TTE18NJ](#) [KQ1008TTER56G](#) [KQT0402TTD27NJ](#) [KQ1008TTER33G](#)
[KQ1008TTER39G](#) [KQ1008TTE1R2G](#) [KQ1008TTE1R8G](#) [KQ1008TTE1R0G](#) [KQ1008TTE1R5G](#) [KQ1008TTE12NJ](#)
[KQ1008TTER75G](#) [KQT0402TTD23NJ](#) [KQ1008TTE6R8G](#) [KQ0603TTE30NG](#) [KQ0805TTE56NG](#) [KQ0603TTE10NG](#)
[KQ0603TTER15G](#) [KQ0603TTER11G](#) [KQ0603TTER10G](#) [KQ0603TTER18G](#) [KQ0603TTER12G](#) [KQ0603TTE22NG](#)
[KQ0603TTE18NJ](#) [KQ0603TTE18NG](#) [KQ1008TTE82NG](#) [KQ1008TTE8R2G](#) [KQ0603TTE24NG](#) [KQ0603TTE36NG](#)
[KQ0603TTE12NG](#) [KQ0603TTE12NJ](#) [KQ0603TTE3N6J](#) [KQ1008TTE68NG](#) [KQ0603TTE3N9J](#) [KQ0603TTE1N8J](#)
[KQ0603TTE1N6J](#) [KQ0603TTER33G](#) [KQ0603TTER39G](#) [KQ0603TTE16NG](#) [KQ0603TTE33NG](#) [KQ0603TTE82NG](#)
[KQ0603TTER27G](#) [KQ0603TTER22G](#) [KQT0402TTD8N2J](#) [KQ0603TTE8N7G](#) [KQ0603TTE39NG](#) [KQT0402TTD9N0J](#)
[KQ0805TTE47NJ](#) [KQ0805TTER82G](#) [KQ0603TTE27NG](#) [KQ1008TTE47NJ](#) [KQT0402TTD5N6J](#) [KQ0603TTE15NJ](#)
[KQ0603TTE15NG](#) [KQT0402TTD40NJ](#) [KQ0603TTE11NG](#) [KQ0805TTE15NJ](#) [KQ0805TTER47G](#) [KQ0805TTE27NJ](#)
[KQ0805TTE39NJ](#) [KQ1008TTE39NJ](#) [KQT0402TTD7N5J](#) [KQ0603LTE3N3J](#) [KQ0805TTE2N8J](#) [KQ0603TTE82NJ](#)
[KQ0603TTER15J](#) [KQ0603TTER18J](#) [KQ0805TTE82NJ](#) [KQ0805TTER56J](#) [KQT0402TTD2N0C](#) [KQ0805TTER22K](#)
[KQT0402TK001-KIT](#) [KQT0402LTD56NJ](#) [KQT0402LTD9N0J](#) [KQ0603TTE8N2G](#)