


NUMBER
C-380306



21/32 Max.



Tool Number	Trip Force	Tip Number	Tip Symbol	Tip Length	"A" Length
* 380306-1	20-22	395005	F	25/32	5 7/16
380306-2	12-13	395005	F	25/32	5 7/16
380306-3	12-13	395042	G	1 5/32	5 7/16
* 380306-4	20-22	395042	G	1 5/32	5 7/16
380306-5	9-10	395005	F	25/32	5 7/16
380306-6	9-10	395042	K	1 5/32	5 7/16
* 380306-7	20-22	380301-1	A1	1 23/32	5 7/16
380306-8	16-18	380301-1	A1	1 23/32	5 7/16
380306-9	12-13	380366-1	C1	1 5/32	5 7/16
1-380306-0	9-10	380339-1	B1	1 3/32	5 7/16
1-380306-1	20-22	395042	G	1 5/32	4 11/16

* 20-22 pound tool to be used exclusively for inserting terminals into receptacles mounted in resilient material. APPLICATION TOOLING ENGR'G. CONNECTOR PRODUCTS DIV.

1. For Tool usage, see Instruction Sheet # 7075 .
2. For Tip dimensions, see Tip Customer Drawing.
3. For readjustment or replacement of parts other than Tips, return Tool to AMP, Inc., Mt. Joy, Penna. to insure proper calibration.
4. Trip force is the force in pounds, required to trip the tool.

DIMENSIONS IN INCHES. DO NOT SCALE PRINT.

©1968 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.				CUSTOMER COPY REFERENCE ONLY	
MATERIAL AND FINISH				AMP INCORPORATED HARRISBURG, PENNA.	
Steel-Plated; Aluminum Weight $3\frac{1}{2} \pm 1\frac{1}{2}$ Oz.					
WIRE — RANGE — INSULATION				TYPE	
TOLERANCE EXCEPT AS NOTED $\pm .015$ $\pm 1^\circ 0'$				SCALE	
LOC				NO	
M				A	
NAME				C-380306	
TOOL-STANDARD CERTI-LOK INSERTION				REV J3	

DR	12/18/62	DE	1/15/63
CHK	1-12-63	APP	1/15/63