

70-378-1 Socket/5 Amp Rating, 120 Volts



Chassis Mounting



BOLD-FACED PART NUMBERS ARE NORMALLY STOCKED

Standard Part Number

Description

70-378-1

14-Pin, Solder Terminals for Chassis mount

General Specifications (UL 508)

Characteristics	Units	Value
Number of Terminals		14
Electrical Rating		
Nominal Voltage Rating	Volts	120
Nominal Current Rating	Amps	5
Dielectric Strength		
Output to Input Terminals	V rms	1500
Output to Adjacent Output Terminals	V rms	1500
Temperature		
Operating Range:	°C	- 40 to + 80
Storage Range:	°C	- 40 to + 105
Construction		
Internal Metal Tracks		Copper Alloy, Zinc Plated
Terminals		Copper Alloy, Zinc Plated
Miscellaneous		
Socket Mounting:		Chassis
Wire Size Capacity (Maximum)	EN 60204-1	AWG mm2
Soild Cu (Output)	AWG, mm2	18 0.8
Stranded Cu (Output)	AWG, mm2	18 0.8
Wire Connection Method		Solder
Flamability Rating	Class	94V-0
Body Color		Light Gray
Product Certification		UL, CSA
Conformance		CE, RoHS
Weight	grams	6.2

782 Relays

16-1324

16-1342

2/49