







REV.	DATE	ECR NO.	DESCRIPTION
NC	11/19/01	XXXXXX	INITIAL RELEASE
A	03/12/03	XXXXXX	UPDATE DRAWING FORMAT
B	08/30/11	2296	REVISE THE FERRULE AND INCREASE THE BARREL'S OD TO .106", ADD STEP DIMENSION
C	08/27/12	2366	ADD INTERFACE DIMENSIONS



RECOMMENDED CABLE STRIPPING DIM'S



PLUG ASSEMBLY



1. IMPEDANCE: 50 OHM
2. FREQUENCY RANGE: 0-6 GHz
3. DIELECTRIC WITHSTANDING VOLTAGE: 500 VRMS. MIN.
4. DURABILITY: 500 CYCLES MIN.
5. TEMPERATURE RANGE: -65°C TO +165°C
6. CRIMP FERRULE
HEX CRIMP SIZE .128"
7. CONTACT PIN TO SOLDER

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.		APPROVALS		DATE		Amphenol Connex									
					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm		DRAWN M.ZHANG		08/30/11											
7	FERRULE	BRASS	GOLD	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"		CHECKED				PART DESCRIPTION									
6	COVER	BRASS	GOLD	1			ISSUED				MMCX R/A CRIMP PLUG (FOR RG-174/U,188A/U,316/U CABLE)									
5	INSULATOR	PTFE	NATURAL	1			SHEET 1 OF 1													
4	RETAINER RING	BER. COPPER	GOLD	1																
3	CONTACT PIN	BRASS	GOLD	1					CAD FILE				PART NO.							
2	INSULATOR	PTFE	NATURAL	1			C:/CONNEX/262103.DWG				262103									
1	BODY WITH HOUSING	BRASS	GOLD	1	DO NOT SCALE DRAWING						DWG. NO.		262103.DWG		REV. C		SIZE A		SCALE NA	
DESCRIPTION		MATERIAL		FINISH		QTY														