

Number of Components: Two
Mix Ratio By Weight: 20:5
Specific Gravity:
Part A 1.15
Part B 0.87
Pot Life: 1 - 2 Hours
Shelf Life: One year at room temperature

Recommended Cure:

65°C 2 Hours

Minimum Alternative Cure(s):

Note: May not achieve performance properties below

65°C 1 Hour

23°C 24 Hours

*Note: Container(s) should be kept closed when not in use. Filled systems should be stirred thoroughly before mixing and prior to use.
- MIXED VOLUME SHOULD NOT EXCEED 25 GRAMS -*

Product Description:

EPO-TEK[®] 301 is a two component, room temperature curing epoxy featuring very low viscosity, and excellent optical-mechanical properties.

EPO-TEK[®] 301 Advantages & Suggested Application Notes:

- Semiconductor: optical glob top or underfill; adhesion to common wafer passivation, solder mask and flex circuits; compatible with LED die, Si, GaAs.
- PCB: general potting and protection over FR4, flex, or ceramic PCBs.
- Medical:
 - It is NONTOXIC—complying with USP Class VI Biocompatibility standards. Suggested for medical devices such as catheters, hand and tooling, dental, and endoscopic products; adhesion to stainless steel, titanium, and most plastics; resisting sterilizing techniques like ETO, gamma, and autoclave (65°C/1 hour cure); resisting X-ray radiation; potting and protection of scintillator crystals; CT Detector packaging; adhesive for the optical beam pathway in photo-diode arrays.
 - Compatible with CIDEX[®] OPA sterilization.
- Fiber Optic: adhesive for glass and plastic fibers; wicking into fiber bundles used in patch cords, endoscopes or sensor devices; adhesive/seal/encapsulant used for fiber packaging and components; transmission of IR up to 2500 nm; terminating fibers into ferrules; fiber coupling and splicing.
- Opto-electronic;
 - LCD/LED adhesive for laminating glass layers; adhesion to PET plastic; general potting, encapsulation, and protection; spectral transmission in VIS and IR light; adhesive/encapsulant for VCSEL's packaged devices; resisting yellowing per ASTM D1925; adhesive for precision optics including lens, prism, beam splitter cubes, mirrors, and diodes, found in medical, university, or research communities.
- NASA approved, low outgassing epoxy – <http://outgassing.nasa.gov/>

Typical Properties: *(To be used as a guide only, not as a specification. Data below is not guaranteed. Different batches, conditions and applications yield differing results; Cure condition: varies as required; * denotes test on lot acceptance basis)*

Physical Properties:	
*Color: Part A: Clear/Colorless Part B: Clear/Colorless	Die Shear Strength @ 23°C: ≥ 10 Kg / 3400 psi
*Consistency: Pourable liquid	Degradation Temp. (TGA): 430°C
*Viscosity (@ 100 RPM/23°C): 100 – 200 cPs	Weight Loss:
Thixotropic Index: N/A	@ 200°C: 0.12%
*Glass Transition Temp.(Tg): ≥ 65°C (Dynamic Cure	@ 250°C: 0.13%
20—200°C /ISO 25 Min; Ramp -10—200°C @ 20°C/Min)	@ 300°C: 0.39%
Coefficient of Thermal Expansion (CTE):	Operating Temp:
Below Tg: 39 x 10 ⁻⁶ in/in/°C	Continuous: - 55°C to 200°C
Above Tg: 98 x 10 ⁻⁶ in/in/°C	Intermittent: - 55°C to 300°C
Shore D Hardness: 85	Storage Modulus @ 23°C: 327,463 psi
Lap Shear Strength @ 23°C: > 2,000 psi	*Particle Size: N/A
Optical Properties @ 23°C:	
Refractive Index @ 23°C (uncured): 1.519 @ 589 nm	Spectral Transmission: >99% 380-980nm >97% 980-1640nm
	>95% 1640-2040nm
Electrical & Thermal Properties:	
Thermal Conductivity: N/A	Volume Resistivity @ 23°C: ≥ 1 x 10 ¹³ Ohm-cm
Dielectric Constant (1 KHz): 4.00	Dissipation Factor (1 KHz): 0.016

EPOXY TECHNOLOGY, INC.

14 Fortune Drive, Billerica, MA 01821-3972 Phone: 978.667.3805 Fax: 978.663.9782

www.EPOTEK.com

Epoxy and Adhesives for Demanding Applications™

This information is based on data and tests believed to be accurate. Epoxy Technology, Inc. makes no warranties (expressed or implied) as to its accuracy and assumes no liability in connection with any use of this product.