


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS				DOC. NO.	SPC-F005	Effective:	12/21/98	DCP No.	860
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
170	A	RELEASED	SAS	07/09/99	JC	6/27/00	DJC	7/11/00	

SPECIFICATIONS:

1. SAFETY SOCKET W/ Ø.080 [2.0] SOLDER HOLE
2. INSULATOR: POLYACETAL
3. CONTACT: BRASS, NICKEL PLATED
4. LOCKING NUT: BRASS, NICKEL PLATED
5. VOLTAGE: 1000V CATIII P2 (IEC1010-1)
6. CURRENT: 25A MAX.
7. RESISTANCE: <5 milliohms
8. TEMPERATURE: -20 °C TO +80 °C.
9. INSULATOR THREAD, M12 X 0.75 6.
10. MAXIMUM PANEL THICKNESS: .40 (10.2).



DISCLAIMER
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY

Tolerances Unless
Otherwise Specified
Fractions ± 1/32
Decimals
.XX ± .01
.XXX ± .005

DRAWN BY:	DATE:
SCOTT SERRITELLA	07/09/99
CHECKED BY:	DATE:
JOHN COLE	6/27/00
APPROVED BY:	DATE:
DANIEL CAREY	7/11/00

DRAWING TITLE:	
SAFETY SOCKET, SOLDER FORK, BLACK	
SIZE	DWG. NO.
A	2270
SCALE:	NTS
U.O.M.: INCHES [mm]	

ELECTRONIC FILE	REV
92N4632.DWG	A
SHEET: 1	OF 1