









Copyright FCI.



rev	ecn no	dr	date
A	T06-0198	TAI	2006-11-27
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface 		tolerance std ASME Y14.5		projection 		MM 	
TOLERANCES UNLESS OTHERWISE SPECIFIED										
Dr	WENDY CHEN	2005-09-22	ANGULAR	LINEAR	0.X	±0.50	size A4	Scale 1.000		
Eng	KENNY TAI	2005-09-22			0.XX	±0.30				
Chr	KENNY TAI	2005-09-22			0.XXX	±0.05				
Appr	PAUL WANG	2005-09-22	0°	±2°	ECN			T06-0198		
Product family					Spec ref			*		
		title TOP MOUNT, CARD PUSH EXPRESSCARD HOST MECH.				dwg no 10061395			Rev. A	
		catalog no 10061395								
		CUSTOMER				sheet 1 of 2				

PART NO.	MOUNTING	STAND-OFF	HOST CONN P/N	PRODUCT SPEC.	PACKING SPEC.
10061395-10ALF	TOP	1.0MM	10059820-X10AXXXLF	GS-12-301	GS-14-295



DETAIL 2
RECOMMENDED SCREW LENGTH

SCALE 1.000

 MOUNTING PART
HEIGHT 0.6MM MAX.

NOTE:

1. 4 M2*0.4P SCREWS WITH WASHER ARE REQUIRED.
2. SHOW DIMENSION AFTER FASTENED TO PCB.
3. SEE HOST CONNECTOR DRAWINGS FOR PCB LAYOUT DETAIL.
4. RECOMMENDED TIGHTING TORQUE 1.6~1.8 KGF-CM.
5. SEE DETAIL 2 FOR RECOMMENDED SCREW LENGTH.

	title TOP MOUNT, CARD PUSH EXPRESSCARD HOST MECH.		dwg no 10061395		Rev A
	catalog no 10061395		CUSTOMER	sheet 2 of 2	