

PART NUMBER	LED COLOR
591-2001-002	HI.EFF. RED
591-2001-007	
591-2001-013	
591-2101-002	AlGaAs RED
591-2101-007	
591-2101-013	
591-2201-002	HI.INTENSITY GREEN
591-2201-007	
591-2201-013	
591-2301-002	GREEN
591-2301-007	
591-2301-013	
591-2401-002	YELLOW
591-2401-007	
591-2401-013	
591-2601-002	BLUE
591-2601-007	
591-2601-013	
591-2701-002	AlInGaP YELLOW
591-2701-007	
591-2701-013	

LED COLOR = HI.EFF. / RED - GREEN - YELLOW						
OPERATING CHARACTERISTICS AT 25°C AMBIENT						
CHARACTERISTICS		MIN	TYP	MAX	UNITS	TEST CONDITIONS
LUMINOUS INTENSITY	RED	5.6	9.8	14.0	mcd	I f = 10 mA
	GREEN	7.1	10.6	14.0		
	YELLOW	7.1	12.6	18.0		
FORWARD VOLTAGE	RED	2.0	2.5		V	I f = 10 mA
	GREEN		2.0	2.5		
	YELLOW		2.0	2.5		
REVERSE VOLTAGE	RED		5		V	I r = 10 µA
	GREEN		5			
	YELLOW		5			
PEAK WAVELENGTH	RED		635		nm	I f = 10 mA
	GREEN		572			
	YELLOW		586			
DOMINANT WAVELENGTH	RED	622	628	634	nm	I f = 10 mA
	GREEN	564	570	576		
	YELLOW	580	587	595		

LED COLOR = HI.EFF. / RED - GREEN - YELLOW			
ABSOLUTE MAXIMUM RATING AT 25°C AMBIENT			
			UNITS
POWER DISSIPATION	RED	95	mW
	GREEN	95	
	YELLOW	95	
CONTINUOUS FORWARD CURRENT	RED	30	mA
	GREEN	30	
	YELLOW	30	
OPERATING TEMPERATURE	R-G-Y	-40 TO 100	°C
STORAGE TEMPERATURE	R-G-Y	-40 TO 100	°C

LED COLOR = RED (AlGaAs) GREEN (HI.INT.) YELLOW (AlInGaP)						
OPERATING CHARACTERISTICS AT 25°C AMBIENT						
CHARACTERISTICS		MIN	TYP	MAX	UNITS	TEST CONDITIONS
LUMINOUS INTENSITY	AlGaAs RED		23.9		mcd	I f = 10 mA
	HI.INT. GREEN		9.1			
	AlInGaP YELLOW		33.6			
FORWARD VOLTAGE	AlGaAs RED		1.8	2.4	V	I f = 20 mA
	HI.INT. GREEN		2.1	2.6		
	AlInGaP YELLOW		2.0	2.4		
REVERSE VOLTAGE	AlGaAs RED		5		V	I f = 10 mA
	HI.INT. GREEN		5			
	AlInGaP YELLOW		5			
DOMINANT WAVELENGTH	AlGaAs RED		638		nm	
	HI.INT. GREEN		569			
	AlInGaP YELLOW		595			


LED COLOR = RED (AlGaAs) GREEN (HI.INT.) YELLOW (AlInGaP)			
ABSOLUTE MAXIMUM RATING AT 25°C AMBIENT			
			UNITS
POWER DISSIPATION	R-G-Y	100	mW
	AlGaAs RED	0.8	
	HI.INT. GREEN	0.6	
DERATE LINEARLY FROM 25°C	AlInGaP YELLOW	0.6	mA/°C
	AlGaAs RED	40	
	HI.INT. GREEN	30	
CONTINUOUS FORWARD CURRENT	AlInGaP YELLOW	50	mA
	AlGaAs RED	200	
	HI.INT. GREEN	120	
PEAK FORWARD CURRENT (1/10 DUTY CYCLE, 0.1 ms PULSE WIDTH)	AlInGaP YELLOW	160	mA
	R-G-Y	-55 TO 100	
	R-G-Y	-55 TO 100	
OPERATING TEMPERATURE	R-G-Y	-55 TO 100	°C
STORAGE TEMPERATURE	R-G-Y	-55 TO 100	°C
INFRARED REFLOW SOLDERING	R-G-Y	260°C FOR 5 SEC	
VAPOR PHASE SOLDERING	R-G-Y	215°C FOR 3 MIN	

LED COLOR = BLUE					
OPERATING CHARACTERISTICS AT 25°C AMBIENT					
CHARACTERISTICS	MIN	TYP	MAX	UNITS	TEST CONDITIONS
LUMINOUS INTENSITY		6.0		mcd	I f = 10 mA
FORWARD VOLTAGE		3.5	4.2	V	I f = 10 mA
REVERSE CURRENT		0.01	10	µA	V r = 5 V





LED COLOR = BLUE		
ABSOLUTE MAXIMUM RATING AT 25°C AMBIENT		
		UNITS
POWER DISSIPATION	100	mW
DERATE LINEARLY FROM 55°C	0.44	mW/°C
CONTINUOUS FORWARD CURRENT	20	mA
OPERATING TEMPERATURE	-40 TO 100	°C
STORAGE TEMPERATURE	-40 TO 100	°C
SOLDER PROFILE: 1R 235°C PEAK FOR 15 sec / 185°C FOR 90 sec MAX		

LED SCHEMATIC

TAPING SPECIFICATION



TOLERANCE: .004 UNLESS OTHERWISE SPECIFIED
MILLIMETER DIMENSIONS SHOWN FOR REFERENCE ONLY



- NOTES :
- 1- MILLIMETER DIMENSIONS SHOWN FOR REFERENCE ONLY
 - 2- PAD NUMBERS ARE FOR REFERENCE ONLY, DESIGNATION NON-EXISTENT ON PART
 - 3- STORAGE CONDITIONS FOR TAPED PRODUCT: RE-TAPING MAY BE NECESSARY FOR PRODUCTS STORED MORE THAN TWELVE MONTHS
 - 4- ORDER QUANTITY IS LED ASSEMBLIES, NOT REELS
 - 5- ...-002 SUFFIX MEANS PARTS ARE PACKED ON A 20 pc SAMPLE STRIP
...-007 SUFFIX MEANS PARTS ARE PACKED ON A 7 INCH REEL, 400 pcs/REEL
...-013 SUFFIX MEANS PARTS ARE PACKED ON A 13 INCH REEL, 1600 pcs/REEL
 - 6- LENS MOVEMENT IN RELATIONSHIP TO THE HOUSING IS:
...-009* T.I.R. VERTICALLY
...-007* T.I.R. HORIZONTALLY
 - 7- FRONT AND REAR TERMINALS OF THE ASSEMBLY TO BE WITHIN .005 COPLANARITY
 - 8- LED LEAD FRAME MATERIAL:
CORE MATERIAL = COPPER
1st PLATING = Ag-100%, THICKNESS ABOUT 90 MICRO-INCH
2nd PLATING = 90% Sn - 10% Pb, THICKNESS RANGE 200 to 800 MICRO-INCH
 - 9- DIALIGHT PART NUMBERS =
591-2x01-002, 591-2x01-007, 591-2x01-013
 10. DEVICE HAS A MOISTURE SENSITIVITY LEVEL "2" CAUTION
LABEL APPLIED AS PER JEDEC STD. 033

REV.	ECN NO.	REVISIONS	DRN.	CKD.	APP.	DATE
A	---	---	---	---	---	---
B	---	---	---	---	---	---
C	---	---	---	---	---	---
D	---	REDRAWN WITH CHANGES -NEW HSG AND LENS DESIGN -ADDED NOTE 6-8 -CHANGE LED CHARACTERISTC	YY	---	NO	3-7-94
E	---	ADDED HI. GREEN AND AlInGaP YELLOW AND CHANGE TO ANOTHER AlGaAs RED CHANGE NOTE 8	AV	DC	NO	3-8-00
F	---	ADD ...2601... (BLUE) CORRECT HI.EFF. LED SPEC	AV	DC	NO	10-10-00
G	---	ADDED NOTE 10	YIS	JMC	NO	2-14-03
H	---	UPDATED LED SPEC. FOR HI.EFF. RED, GREEN & YELLOW	YIS			

THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT.		DRAWING NUMBER		REV
SCALE 8:1		C-15636		H
ALL DIM'S IN: INCHES		TITLE		
TOLERANCES: UNLESS OTHERWISE SPECIFIED		SURFACE MOUNT CBI - ROUND LENS		
FRACTIONS: ±1/64		MATERIAL		
DECIMALS (.XX): ±.020		Dialight		
DECIMALS (.XXX): ±.015				
DECIMALS (.XXXX): ±.005				
ANGLES: ±3°		1501 ROUTE 34 SOUTH FARMINGDALE, NJ 07727		
FINISH: ±3°		SHEET OF FAMILY TABLES:		
FSCM 83330				