

GP Series Sealed Ultraminiature Pushbutton Switches




Features/Benefits

- Ultraminiature design saves space
- Process compatible, withstands most soldering and washing processes
- Thru-hole and surface mount models available
- Sealed construction—internal o-ring and epoxy base
- RoHS compliant

Typical Applications

- Telecommunications and network equipment
- Computers and peripheral products
- Instrumentation
- Medical Applications



Specifications

CONTACT RATING: 0.4 VA max. @ 20 V AC or DC max.

MECHANICAL & ELECTRICAL LIFE: 40,000 make-and-break cycles at full load.

CONTACT RESISTANCE: Below 50 mΩ typ. initial @ 2-4 V DC, 100 mA.

INSULATION RESISTANCE: $10^9 \Omega$ min.

DIELECTRIC STRENGTH: 500 Vrms min. @ sea level.

OPERATING TEMPERATURE: -40°C to 85°C.

SOLDERABILITY: Per MIL-STD-202F method 208D, or EIA RS-186E method 9 (1 hour steam aging).

DEGREE OF PROTECTION: IP57; Protection against harmful dust deposit, full-scale voltage protection, temporary immersion.

PACKAGING: Surface mount switches standard in anti-static tape and reel packaging per EIA 481-3, see page A-80 for drawings and reel information. Thru-Hole parts are shipped in trays.

All models are RoHS compliant and compliant.

Materials

HOUSING & BASE: Glass filled nylon 4/6, flame retardant, heat stabilized (UL 94V-0).

ACTUATOR: Glass filled nylon 4/6, flame retardant (UL 94V-0) with standard internal o-ring seal.

SWITCH SUPPORT: Brass, tin plated.

MOVABLE CONTACT: Copper alloy, with gold plate over nickel plate.

STATIONARY CONTACTS: Copper alloy, with gold plate over nickel plate.

TERMINALS: Copper alloy, with gold flash over nickel plate.

TERMINAL SEAL: Epoxy/Urethane. All terminals insert molded.

NOTE: Any models supplied with B contact material are RoHS compliant and compatible.

NOTE: Materials listed above are general specifications. Specifications available for specific and custom switches, consult Customer Service Center.

CAUTION: PC mounting layouts and pads as shown are designed to be compatible with the latest equipment and reflow techniques. Care should be taken in the design and location of PC lands to suit individual needs. Orientation relative to reflow direction may significantly impact solder joint integrity.


How To Order

Complete part numbers for GP Series Sealed Ultraminiature Pushbutton Switches are shown on pages A-78 thru A-80.


PART NUMBER	SWITCH FUNCTION		SCHEMATIC
	POS.1	POS. 2	
GP11MCBE	OFF	MOM.	
Conn. Terms.	OPEN	1-3	SPST

PART NUMBER	SWITCH FUNCTION	SCHEMATIC	PC MOUNTING	
			PC LANDS	PC PADS
GP12MCBE	ON	MOM.		
Conn. Terms.	2-1	2-3	SPDT	GP11- omit center hole.

MOM. = Momentary



GP11MCBE
SPST



GP12 Model






Dimensions are shown: Inches (mm)
Specifications and dimensions subject to change

www.ck-components.com




GP Series

Sealed Ultraminiature Pushbutton Switches

GP11MABE
SPSTGP11MSABE
SPST


PART NUMBER	SWITCH FUNCTION		SCHEMATIC
	POS.1	POS. 2	
GP11MABE	OFF	MOM.	
Conn. Terms.	OPEN	1-3	SPST
GP12MABE	ON	MOM.	
Conn. Terms.	2-1	2-3	SPDT

MOM. = Momentary

GP11MSA1BE
SPST

PART NUMBER	SWITCH FUNCTION		SCHEMATIC
	POS.1	POS. 2	
GP11MSA1BE	OFF	MOM.	
Conn. Terms.	OPEN	1-3	SPST
GP12MSA1BE	ON	MOM.	
Conn. Terms.	2-1	2-3	SPDT

MOM. = Momentary

Dimensions are shown: Inches (mm)
Specifications and dimensions subject to change


GP Series Sealed Ultraminiature Pushbutton Switches



Pushbutton


PART NUMBER	SWITCH FUNCTION		SCHEMATIC
	POS.1	POS. 2	
GP12MSCBE	ON	MOM.	NC 1 2 (COMM) 3 NO
Conn. Terms.	2-1	2-3	SPDT

MOM. = Momentary



GP12MSCBE
SPDT

PC MOUNTING




NOTE: Recommended for infrequent use applications only
For increased switch mounting strength, order, SV1 termination
style with support bracket (see below).



PART NUMBER	SWITCH FUNCTION		SCHEMATIC
	POS.1	POS. 2	
GP11MSV1BE	OFF	MOM.	1 3
Conn. Terms.	OPEN	1-3	SPST

PART NUMBER	SWITCH FUNCTION		SCHEMATIC
	POS.1	POS. 2	
GP12MSV1BE	ON	MOM.	NC 1 2 (COMM) 3 NO
Conn. Terms.	2-1	2-3	SPDT

MOM. = Momentary





GP11MSV1BE
SPST



GP12 Model

Terminal nos.
for reference only.



Dimensions are shown: Inches (mm)
Specifications and dimensions subject to change

www.ck-components.com




GP Series

Sealed Ultraminiature Pushbutton Switches

TAPE & REEL


For part numbers GP11MSV1BE, GP12MSV1BE

REEL INFORMATION	
OUTSIDE DIAMETER	13.00 (330,0)
PILOT HOLE	.512 (13,0)
QUANTITY PER REEL	600





For part numbers GP11SA1BE, GP11MSBE

REEL INFORMATION	
OUTSIDE DIAMETER	13.00 (330,0)
PILOT HOLE	.512 (13,0)
QUANTITY PER REEL	600



For part numbers GP12MSCBE

REEL INFORMATION	
OUTSIDE DIAMETER	13.00 (330,0)
PILOT HOLE	.512 (13,0)
QUANTITY PER REEL	600



Dimensions are shown: Inches (mm)
Specifications and dimensions subject to change

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

C&K Components:

[GP11MAKE](#) [GP11MCKE](#) [GP11MCBE](#) [GP11MABE](#) [GP12MSC1KE](#) [GP12MSA1BE](#) [GP11MSA1BE](#) [GP11MSABE](#)
[GP11MSV1BE](#) [GP12MABE](#) [GP12MCBE](#) [GP12MSABE](#) [GP12MSCBE](#) [GP12MSV1BE](#)