





LOC	DIST	P	F	REVISIONS						
				ZONE	LTR	DESCRIPTION			DATE	APPD
AA	22				M	REV; EC 0502-0711-97			23OCT97	DS EL



- 1 MATERIAL: HOUSING- HTN MOLDING COMPOUND, 94V0, BLACK.
TERMINAL- 0.36 [.014] THICK PHOS BRONZE PLATED WITH 1.27μm [.000050] THICK HARD GOLD IN LOCALIZED GOLD PLATE AREA AND 2.03μm [.000150] THICK TIN-LEAD IN SOLDER AREA OVER 1.27μm [.000050] THICK NICKEL UNDERPLATE.
- 2 CAVITY CONFORMS TO FCC RULES AND REGULATIONS PART 68, SUBPART F.
3. SNAP-IN RETENTION FEATURE ACCOMMODATES A 1.57±0.13 [.062±.005] THICK PRINTED CIRCUIT BOARD.
- 4 DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED AND ARE PRIOR TO SURFACE MOUNT PROCESSING.
- 5 TERMINALS ASSEMBLED IN CENTER POSITIONS FOR -2.



PRINTED CIRCUIT BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

		NUMBER OF TERMINALS		PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ±- 3 PLC DEC ±- ANGLES ±- △ 4	DR 9-27-95 D. STRAUSSER		AMP AMP Incorporated Harrisburg, PA 17105-3608		
	CHK 10-17-95 N. JONES				
	APPD 10-23-95 J. TONEY		NAME MODULAR JACK ASSEMBLY, 6 POSITION, LOW PROFILE, RIGHT ANGLE, SURFACE MOUNT WITH PANEL STOPS		
	APPD 10-24-95 H. MCGRATH				
MATERIAL △ 1	PRODUCT SPEC 108-1163				
FINISH △ 1	APPLICATION SPEC 114-6040		SIZE Ⓒ	CAGE CODE 00779	DRAWING NO Ⓒ=555077
	WEIGHT —		SCALE 4:1		SHEET 1 OF 1