

HCC 4-F

Order No.: 1600001



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1600001>

Female insert, Type of connection: Screw connection, Screw connection, Cross section: 0.2 mm² - 4 mm², AWG 24 - 12, Width: 92 mm, Height: 18 mm, Color: gray

Commercial data

EAN	4017918021733
Pack	50 pcs.
Customs tariff	85366990
Weight/Piece	0.04348 KG
Catalog page information	Page 299 (CL-2009)

Product notes

WEEE/RoHS-compliant since: 09/08/2005



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Certificates / Approvals



Certification

BV, CSA, DNV, GL, LR, UL

CSA

Nominal voltage U_N	300 V
Nominal current I_N	20 A
AWG/kcmil	28-10

UL

Nominal voltage U_N	300 V
Nominal current I_N	20 A
AWG/kcmil	30-10

Accessories

Item	Designation	Description
------	-------------	-------------

Assembly

1600069	HCC 4-FE	Foot element, Color: gray
---------	----------	---------------------------

Plug/Adapter

1600027	CP-HCC 4	Coding profile, Color: red
3100224	HCC 4-SR	Strain relief, Color: gray

Tools

1205053	SZS 0,6X3,5	Screwdriver, bladed, matches all screw terminal blocks up to 4.0 mm ² connection cross section, blade: 0.6 x 3.5 mm, without VDE approval
---------	-------------	--

Additional products



Item	Designation	Description
------	-------------	-------------

General


1600014	HCC 4-M	Plug, Type of connection: Screw connection, Screw connection, Cross section: 0.2 mm ² - 4 mm ² , AWG 24 - 12, Width: 92 mm, Height: 18 mm, Color: gray, Mounting type: Direct screw connection
---------	---------	--

Diagrams/Drawings

Diagram



Dimensioned drawing



Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;