

Solutions for
Electronic Specialty
Markets (ESM)

Product Catalog
for Electronic
Specialty Markets

- 3M® Electronic Specialty Markets New Product Releases
- 3M® Abrasives
- 3M® Adhesives, Cleaners & Compounds
- 3M® Breadboards & Test Clips
- 3M® Cable & Assemblies
- 3M® Copper Interconnects
- 3M® Fiber Optics
- 3M® Fire Protection
- 3M® Heat Shrink
- 3M® Identification Systems
- 3M® Occupational Health & Safety Products
- 3M® Protective Bumpers
- 3M® Reclosable Fasteners
- 3M® Splicing, Terminating & Ducting
- 3M® Static Control
- 3M® Tapes
- 3M® Terminals, Kits & Tools
- 3M® Vacuums & Accessories
- 3M® Warehousing & Packaging Supplies
- 3M® Wire Connectors

Other Tools

- What's New
- Sales Contacts
- U.S. Distributors

Search This Product Catalog


By Keyword

Go

[Product Catalog for Electronic Specialty Markets](#) [3M® Terminals, Kits & Tools](#) [Disconnects](#)
[Scotchlok® Female Disconnects - Non-Insulated Butted Seam](#)

3M® Scotchlok® Non-Insulated Butted
Seam Female Disconnect MU14 -250DFX, 16-14 AWG

 [Printer-friendly format](#)



This disconnect has a wire range of 16 - 14 AWG and a quantity of 100 per carton and 500 per case.

[\[click to
enlarge\]](#)

GTIN(UPC/EAN) : 0 00 54007 22849 3
3M Id : 80 - 6013 - 1190 - 7

Additional Information

The disconnects are attached to mating part by tongue of female part slipping over male tab. The use of dents and rolled edges on female part provides excellent holding force while allowing easy and quick disconnect.

Learn More . . .

- [Packaging Data](#)
- [Female Disconnects - Non-Insulated Butted Seam - Product Selection Guide \(PDF 15.7 K\)](#)
- [Scotchlok Terminals MU18 -250DF, MU14 -250DF - Data Sheet \(PDF 32.8 K\)](#)
- [Terminal Stud Size Chart - Product Selection Guide \(PDF 5.2 K\)](#)

Please Note:
Adobe® Acrobat® Reader is required to view PDF documents.



Characteristics

Agency Approvals	UL and CSA
Barrel Style	Butted
China RoHS - Below MCV	Yes
CSA File Number	LR22190
EPC Can View	Public
EU RoHS Compliant	Yes
Fastener Orientation	Female
Pad Width	0.250 Inch
Terminal Style	Standard
Terminal Type	Disconnect
UL File Number	E70512
Wire Gauge Range	14 to 16 American Wire Gauge (AWG)