






1 2 3 4 5 6 7 8

A

B

C

(26.60)
PROTECTIVE CAP WIDTH



A

B


C

D

E

F

NOTE 12



NOTE 13


B
VIEWS SHOWN WITH
PROTECTIVE COVER INSTALLED
10123360-101LF & 111LF

D

E

F

Copyright FCI.
FCI

spec ref		-		dr		Sander Soe		2012/11/15		projection		MM		size		A2		scale		5:1			
tolerance std		ASME Y14.5		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		Kou Xu		2014/08/11						ecn no		ELX-DG-18510-1					
				chr		-		-								rel level		Released					
				appr		Collins Lu		2014/10/23		product family						AIRMAX VS							
surface		✓		linear		0.X		±0.3				title		AIRMAX VSE VERTICAL HEADER		dwg no		10123360		rev		B	
				0.XX		±0.10		5 PAIR 150 POS 2MM 10 COL SMALL PRESS FIT															
				0.XXX		±0.050																	
ASME Y14.5				angular		0°		±2°		www.fci.com		cat. no.		-		Product - Customer Drw		sheet 2 of 4					

PDS: Rev :B

STATUS:Released


Printed: Oct 24, 2014

2


3

4

5



RECOMMENDED PCB LAYOUT
FOR DIFFERENTIAL APPLICATIONS,
COMPONENT SIDE
(TWO ADJACENT FOOTPRINTS SHOWN)
NOTES 6, AND 8

spec ref -		dr Sander Soe		2012/11/15		projection 	MM 	size A2	scale 3:1
tolerance std ASME Y14.5 -	TOLERANCES UNLESS OTHERWISE SPECIFIED		eng Kou Xu	2014/08/11				ecn no ELX-DG-18510-1	
			chr -	-				rel level Released	
			appr Collins Lu	2014/10/23					
product family AIRMAX VS									
surface 	linear	0.X	±0.3		title AIRMAX VSE VERTICAL HEADER 5 PAIR 150 POS 2MM 10 COL SMALL PRESS FIT	dwg no 10123360	rev B		
		0.XX	±0.10						
		0.XXX	±0.050						
	ASME Y14.5	angular	0°					±2°	
www.fci.com		cat. no.	-	Product- Customer Drw			sheet 3 of 4		

