



LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			N	REVISED PER ECO-14-000066	26JUN2014	NK	MM



RECOMMENDED HOLE LAYOUT

SUPERSEDED BY 6-146269-5	7 OBSOLETE	3.084	3.000	30	62	2-104350-1			
		3.984	3.900	39	80	2-104350-0			
		OBSOLETE 7	2.984	2.900	29	60	1-104350-9		
			2.484	2.400	24	50	1-104350-8		
			1.984	1.900	19	40	1-104350-7		
	OBSOLETE 7	1.684	1.600	16	34	1-104350-6			
		1.484	1.400	14	30	1-104350-5			
		1.384	1.300	13	28	1-104350-4			
		1.284	1.200	12	26	1-104350-3			
		1.184	1.100	11	24	1-104350-2			
7 OBSOLETE	OBSOLETE 7	1.084	1.000	10	22	1-104350-1			
		.984	.900	9	20	1-104350-0			
		.884	.800	8	18	104350-9			
		.784	.700	7	16	104350-8			
		.684	.600	6	14	104350-7			
		.584	.500	5	12	104350-6			
		.484	.400	4	10	104350-5			
		.384	.300	3	8	104350-4			
		.284	.200	2	6	104350-3			
		.184	.100	1	4	104350-2			
C	B	A	NO OF POSN	ASSEMBLY PART NUMBER	.084	—	—	2	104350-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN: H MOLL 08FE888		 TE Connectivity	
		CHK: R. FEIDT 08FE888			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
INCHES		APVD: R. FEIDT 08FE888			
		0 PLC ± —		PRODUCT SPEC	
		1 PLC ± —		—	
		2 PLC ± —		—	
		3 PLC ± .005		APPLICATION SPEC	
4 PLC ± —		4 PLC ± —		—	
ANGLES		—		—	
MATERIAL HOUSING FLAME RETARDANT THERMOPLASTIC COLOR-BLACK		FINISH POST: 00000 000 IN CONTACT AREA 000100-000200 MATTE TN-LINK OR SOLDER SML ALL OVER 000000 MOUNT		RESTRICTED TO	
TYP: COPPER ALLOY		WEIGHT —		—	
CUSTOMER DRAWING		A1		DRAWING NO. 104350	
		SCALE 4:1		SHEET 1 OF 1 REV N	