





MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



1500	350	200	10A	5	45	70	70
	85°C	125 °C		10 MHz	100 MHz	1 GHz	10 GHz
MIN. CAP. (pF)	WORKING VOLTAGE (VDC)		CURRENT (Idc)	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD -220			

X-2015 Rev-0

REVISION RECORD		0		1		2		3		4				
Original Release C.O.		WAS SK 6644-001-S. L.E. 01-13-84		DIM'S & TOL'S REV'D RELEASED. S.M. 02-02-01		1653		CURRENT UNIT "A" ADDED. L.E. 08-20-85		2585				
										RDN TO COMP FMT & ADDED METRIC. S.M. 02-02-01				
										20010202-2-01				
												--TOLERANCES-- Unless Otherwise Specified	Title	
												DECIMAL ± .031 [0.79]		
												ANGLES ±	Drawn S.M. 02-02-01	Scale 3 X
												TUSONIX TUCSON, ARIZONA	Approved T.C. 02-02-01	
													A	4202-001

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix:](#)

[4202-001LF](#)