

Customer Information Sheet

DRAWING No.: M80-888XXXX

SHEET 2 OF 2

IF IN DOUBT - ASK

C

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

SPECIFICATION:**MATERIAL:**

MOULDING = GLASS-FILLED PBT UL94V-0, BLACK

CLIP = BERYLLIUM COPPER

SHELL = COPPER ALLOY

FINISH (ALL OVER NICKEL):**CONTACTS:**01 = 0.30 μ GOLD CLIP, 4.0 μ 100% TIN SHELL05 = 0.30 μ GOLD CLIP, 0.28 μ GOLD SHELL**ELECTRICAL:**

CURRENT RATING AT 25°C = 3.0A MAX

CURRENT RATING AT 85°C = 2.2A MAX

WORKING VOLTAGE = 120V AC/DC

VOLTAGE PROOF = 360V AC/DC

CONTACT RESISTANCE:INITIAL = 20m Ω MAXAFTER CONDITIONING = 25m Ω MAX**INSULATION RESISTANCE:**INITIAL = 1000M Ω MINAFTER CONDITIONING = 100M Ω MIN**MECHANICAL:**

DURABILITY = 500 OPERATIONS

INSERTION FORCE = 2.8N MAX, 1.0N MIN

WITHDRAWAL FORCE = 1.8N MAX, 0.2N MIN

ENVIRONMENTAL:



TEMPERATURE RANGE = -55°C TO +125°C

PACKING:

BAG (CONTACTS AND MOULDINGS UN-ASSEMBLED)

NOTES:

1. RECOMMENDED WIRE TYPE = BS3G210 TYPE A, PTFE INSULATED, 24-28 AWG. MAX INSULATION DIAMETER = $\varnothing$ 1.10mm, STRIP WIRE BY 2.00mm.
2. RECOMMENDED HAND CRIMP TOOL = M22520/2-01 WITH POSITIONER T5747. REFER TO INSTRUCTION SHEET IS-01 FOR COMPLETE CRIMPING INSTRUCTIONS.
3. CONTACT INSERTION AND EXTRACTION TOOL = Z80-280. REFER TO INSTRUCTION SHEET IS-25 FOR ASSEMBLY INSTRUCTIONS.

COMMERCIAL
ORDER CODE:**M80-888XXXX**

TOTAL No. OF WAYS

04 - 20, 26, 34

FINISH:

01 - GOLD CLIP, 100% TIN SHELL

05 - GOLD CLIP, GOLD SHELL

BRITISH STANDARD

ORDER CODE: TO BS9525 F0033

B5740-2XX-F-C-X

TOTAL No. OF WAYS

04 - 20, 26, 34

FINISH:

0 - GOLD CLIP, 100% TIN SHELL

2 - GOLD CLIP, GOLD SHELL

SM	13	08.08.11	11389
NAME	ISS.	DATE	C/NOTE
APPROVED: S. MCCULLAGH			
CHECKED: R. ADDE			
DRAWN: W. J. BOURNE			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

HARWIN USA TEL: 603 893 5376 FAX: 603 893 5396 mis@harwin.com	HARWIN Europe (UK) TEL: 023 9231 4545 FAX: 023 9231 4590 mis@harwin.co.uk	HARWIN Asia TEL: +65 6 779 4909 FAX: +65 6 779 3868 mis@harwin.com.sg
--	--	--

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES

X. = $\pm$ 1mm
X.X = $\pm$ 0.25mm
X.XX = $\pm$ 0.10mm
X.XXX = $\pm$ 0.01mm

ANGLES = $\pm$ 5°

UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH: SEE ABOVE

S/AREA:

mm²

TITLE: DATAMATE 2mm PITCH
CRIMP DIL SOCKET ASSY
SMALL BORE (24-28 AWG)

DRAWING NUMBER:

M80-888XXXXSHT
2
OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Harwin:

[M80-8880405](#) [M80-8881605](#) [M80-8883405](#) [M80-8881005](#) [M80-8880605](#) [M80-8882605](#) [M80-8880805](#) [M80-8881205](#) [M80-8882005](#) [M80-8881805](#) [M80-8881405](#) [B5740-218-F-C-2](#) [B5740-208-F-C-2](#) [B5740-226-F-C-2](#) [B5740-220-F-C-2](#) [B5740-206-F-C-2](#) [B5740-204-F-C-2](#) [B5740-214-F-C-2](#) [B5740-210-F-C-2](#) [B5740-216-F-C-2](#) [B5740-212-F-C-2](#) [B5740-234-F-C-2](#) [M80-8880401](#)