



**Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.**



CAP. (pF) MIN.	125° Working Voltage	Current V.D.C.	Minimum No Load Insertion Loss (dB) at 25°C per Mil-Std-220				
			10 MHz	20 MHz	100 MHz	400 MHz	10 GHz
12,000	70 VDC	10 A	22	30	70	65	65

MIL P/N
M15733/62-0004

REVISION RECORD Original Release C.O. WAS SK 7097-001. E.C. 06-14-93 0 930528-2 DWG. REVISED, E.C. 07-07-93 1 930623-1 DWG. REVISED, E.C. 02-24-94 2 940216-6 REDRAWN ON COMP. & UPDATED DWG. S.M. 07-10-98 3 19980707-3-01 ADDED MIN. TO CAP. S.M. 08-27-98 4 19980806-6-02 CAP WAS MIN. 12,000. S.M. 09-02-98 5 19980902-1-01 CAP WAS 12,000/20,000. S.M. 05-28-99 6 19980908-5-01	--TOLERANCES-- Unless Otherwise Specified		Title EMI FILTER MIL-F-15733	
	DECIMAL ± .031			
	ANGLES ± 		Drawn S.M. 07-10-98 Scale 8 X	
	TUSONIX TUCSON, ARIZONA		Approved H.R. 07-10-98	
			A	4151-500

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix:](#)

[4151-500](#)