

C. Webster 11-30-90
APPROVED/DATE

SAFETY ORGANIZATION(S):

THIS FILTER HAS BEEN FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS HAVE BEEN MET.

UL RECOGNIZED
UL 1283
CSA CERTIFIED (PENDING)
CSA 22.2, NO.0,0.4,8
VDE APPROVED (PENDING)
VDE 565-3

OPERATING SPECIFICATIONS:
LINE VOLTAGE/CURRENT:

1 AMP., 120/250 VAC
1 AMP./40°C, 250 VAC
50-60Hz

LINE FREQUENCY:

MAX. LEAKAGE CURRENT, EACH
LINE TO GROUND

.25 mA @ 120V 60 Hz
.48 mA @ 250V 50 Hz

OPERATING AMBIENT TEMP. RANGE:

-10°C TO +40°C @ RATED CURRENT, I_r

IN AN AMBIENT, T_a , HIGHER THAN 40°C, THE MAXIMUM OPERATING
CURRENT, I_o , IS AS FOLLOWS:

$$I_o = I_r \sqrt{\frac{85-T_a}{45}}$$

RELIABILITY SPECIFICATIONS:

STORAGE TEMPERATURE:

-40°C TO +85°C

HUMIDITY:

21 DAYS @ 40°C 95% RH

CURRENT OVERLOAD TEST:

6 TIMES RATED CURRENT FOR 8 SECONDS

TEST SPECIFICATIONS:

INDUCTANCE:

1.86 mH NOMINAL

CAPACITANCE, (MEASURED @ 1 KHz, 0.25 VAC MAX., 25°C ±1°C)

.003μF ±20%

LINE TO GROUND:

.81μF ±20%

LINE TO LINE:

330kΩ

DISCHARGE RESISTOR

6000 MΩ (MIN) AT 100 VDC

LINE/GROUND AND LINE/LINE

20°C AND 50% RH

INSULATION RESISTANCE

RECOMMENDED RECEIVING INSPECTION HIPOT:

2250 VDC FOR 1 MINUTE

LINE TO GROUND:

1450 VDC FOR 1 MINUTE

LINE TO LINE:


FILTER APPROVAL:

THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING
TO TEST THE UNIT IN YOUR EQUIPMENT.

50n - 50n (MINIMUM) INSERTION LOSS

FREQUENCY MHz	.15	.5	1	2	5	10	20	30
COMMON dB	18	32	40	45	45	45	52	40
DIFF. dB	20	50	65	65	60	53	48	48

This document is proprietary to CORCOM INC. and is not
to be reproduced nor used for manufacturing purposes
except on CORCOM's order or prior written consent.



corcom
LIBERTYVILLE, IL 60048

POWER LINE FILTER

SCALE: NTS 11-5-90
REV. BY: CFM
ORIG. NO.: 1EDK3.00
REV.