






NOTES
BEMERKUNGEN

NV NOTE NOT VALID
Bemerkung nicht verwendet

1 ORDER NUMBER
BESTELL-NUMMER

2 REVISION NUMBER
WERKZEUGÄNDERUNGSINDEX

3 MATERIAL MARKING
WERKSTOFFKENNZEICHNUNG

NV GM LOGO
GM Logo



5 PRODUCTION DATE
PRODUKTIONSdatum

6 CONTACT CAVITY NUMBER
KONTAKTKAMMERNUMMER

7 TE LOGO
TE Logo

8 PACKAGING; BULK MATERIAL IN CARDBOARD BOX
VERPACKUNG; SCHUTTGUT IN KARTON

9 TOOL CAVITY MARKING
NESTMARKIERUNG



A4	114-18987	SCHNITTSTELLEZEICHNUNG Interface Drawing
	929103	2 Pos. TAB 1.6x0.6 TAB-Hsg.
	1563190	2 Pos. TAB 1.6x0.6, TAB-Hsg.
	TE BESTELL-NR. TE ORDER NO.	BENENNUNG DESCRIPTION
	COUNTERPARTS GEGENSTECKER	

13106617	0-1241844-2	1.5	CuFe 2	PRETINNED
13106617	0-0964263-2	0.5-1.0	CuFe 2	PRETINNED
13106617	0-0964261-2	0.35-0.5	CuFe 2	PRETINNED
GM NO	TE ORDER NO STRIP FORM	WIRE RANGE MM ²	MATERIAL	FINISH

RECOMMENDED CONTACT SYSTEM: MICRO TIMER 2 TYPE A; UNSEALED
FOR CABLE INSULATION TYPE FLR ACC. DIN 72551 / ISO 6722 MAX. WIRE SIZE 1.5mm²
MAX. CABLE ISOLATION CRIMP DIAMETER 2.9mm
FOR CABLE INSULATION TYPE TXL ACC. SAE J1128 MAX. WIRE SIZE 1.0mm² OR MAX AWG 18
THE USE OF OTHER CABLE TYPES MUST BE CHECKED IN ANY INDIVIDUAL CASE!

	A4								
A3	F2-48	24414864	0-1563189-3	A	2 Pos. MT2, Rec-Hsg. CODZ	NATUR	PBT-GF20	0.9	1
	-	-	0-1563189-2	A	2 Pos. MT2, Rec-Hsg. CODB	Hd	PBT-GF20	0.9	1
	GF2-50	19179871	0-1563189-1	A	2 Pos. MT2, Rec-Hsg. CODA	BLACK	PBT-GF20	0.9	1
	CUSTOMER ABBR. NO	GM PART NO	PART NO	REV	DESCRIPTION	COLOR	MATERIAL	WEIGHT [g]	ITEM NO

THIS DRAWING IS A CONTROLLED DOCUMENT FOR ISO ELECTRONICS CORPORATION DATE 17 10 2008 BY: [Signature] CHECKED BY: [Signature] IT IS THE RESPONSIBILITY OF THE USER TO CONTACT THE DRAWING ORIGINATOR WHENEVER HE IS REQUIRED FOR THE LATEST REVISION.						DWG C. Anghel 29JUN2007		
						CHK A. Ketteler 29JUN2007		
								tyco Electronics AMP GmbH 66265 Bensheim (Germany)
DIMENSIONS:						APVD - NAME	2 Pos. MT2. Rec. Hsg.	
mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: (A2)				PRODUCT SPEC - 108-94118 - APPLICATION SPEC 114-18901		
		0 PLC ±0.5 1 PLC ±0.5 2 PLC ±0.5 3 PLC ±0.5 4 PLC ±0.5 ANGLES ±°				SIZE CAGE CODE DRAWING NO RESTRICTED TO A 00779 C=1563189 -		
MATERIAL	-	FINISH -				WEIGHT -		
CUSTOMER DRAWING						SCALE 5:1 SHEET 1 of 1 REV A4		