


**Order No.: 1017493**

**Type: TDPT 2,5/ 4-SC-5,08**

**PCB terminal block, Screw connection with tension sleeve**



The figure shows a 10-position version of the product

## 1 Main features



- |                           |                                      |                        |                     |
|---------------------------|--------------------------------------|------------------------|---------------------|
| • No. of pos.             | 4                                    | • Nominal current      | 24 A                |
| • Conductor cross section | 2.5 mm <sup>2</sup>                  | • Nominal voltage      | 400 V               |
| • Color                   | green                                | • Connection direction | 0 °                 |
| • Pitch                   | 5.08 mm                              | • Type of packaging    | packed in cardboard |
| • Connection method       | Screw connection with tension sleeve |                        |                     |

## 2 Your advantages

- ✓ Easy to adapt, thanks to their identical size and the same pinning for Push-in spring connections as for screw connections
- ✓ Well-known connection principle allows worldwide use
- ✓ Low temperature rise, thanks to maximum contact force




Make sure you always use the latest documentation.  
It can be downloaded at: [phoenixcontact.net/product/1017493](https://phoenixcontact.net/product/1017493)

**1017493 TDPT 2,5/ 4-SC-5,08****3 Table of contents**

|    |                                                              |   |
|----|--------------------------------------------------------------|---|
| 1  | Main features .....                                          | 1 |
| 2  | Your advantages .....                                        | 1 |
| 3  | Table of contents .....                                      | 2 |
| 4  | 3D model in PDF can be activated (Acrobat Reader only) ..... | 3 |
| 5  | item properties .....                                        | 4 |
|    | 5.1 Connection capacity .....                                | 4 |
|    | 5.2 Material data .....                                      | 4 |
| 6  | Dimensions .....                                             | 4 |
|    | 6.1 Dimensions for the product .....                         | 4 |
|    | 6.2 Dimensions for PCB design .....                          | 5 |
| 7  | Series drawing .....                                         | 6 |
| 8  | Packaging information .....                                  | 7 |
| 9  | Application .....                                            | 7 |
|    | 9.1 Temperature limit values .....                           | 7 |
|    | 9.2 Electrical data .....                                    | 7 |
| 10 | Approvals .....                                              | 7 |
| 11 | Commercial Data .....                                        | 8 |
| 12 | Accessories .....                                            | 8 |

1017493 TDPT 2,5/ 4-SC-5,08

#### 4 3D model in PDF can be activated (Acrobat Reader only)



**1017493 TDPT 2,5/ 4-SC-5,08****5 item properties**

|                       |                                      |
|-----------------------|--------------------------------------|
| Order No.             | 1017493                              |
| Type                  | TDPT 2,5/ 4-SC-5,08                  |
| Range of articles     | TDPT 2,5/...-SC                      |
| Pitch                 | 5.08 mm                              |
| Number of positions   | 4                                    |
| Connection method     | Screw connection with tension sleeve |
| Drive form screw head | Slotted (L)                          |
| Mounting type         | Wave soldering                       |
| Pin layout            | Linear double pinning                |

**5.1 Connection capacity**

|                                                                                        |                                             |
|----------------------------------------------------------------------------------------|---------------------------------------------|
| Conductor cross section, solid                                                         | 0.2 mm <sup>2</sup> to 4 mm <sup>2</sup>    |
| Conductor cross section, flexible                                                      | 0.2 mm <sup>2</sup> to 2.5 mm <sup>2</sup>  |
| Conductor cross section AWG/kcmil                                                      | 24 to 12                                    |
| 2 conductors with same cross section, solid                                            | 0.2 mm <sup>2</sup> to 1.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded                                         | 0.2 mm <sup>2</sup> to 1.5 mm <sup>2</sup>  |
| Conductor cross section flexible, with ferrule without plastic sleeve                  | 0.2 mm <sup>2</sup> to 2.5 mm <sup>2</sup>  |
| Conductor cross section flexible, with ferrule with plastic sleeve                     | 0.2 mm <sup>2</sup> to 2.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded, with TWIN ferrules with plastic sleeve | 0.5 mm <sup>2</sup> to 0.75 mm <sup>2</sup> |
| Stripping length                                                                       | 10 mm                                       |

**5.2 Material data**

|                                        |                                                                         |         |
|----------------------------------------|-------------------------------------------------------------------------|---------|
| Material of metal parts                |                                                                         |         |
| Note                                   | WEEE/RoHS-compliant, whisker-free acc. to IEC 60068-2-82/JEDEC JESD 201 |         |
| Contact material                       | Cu alloy                                                                |         |
| Surface characteristics                | hot-dip tin-plated                                                      |         |
| Insulating material data               | Housing                                                                 | Housing |
| Insulating material                    |                                                                         |         |
| CTI according to IEC 60112             |                                                                         |         |
| Flammability rating according to UL 94 |                                                                         |         |
| Color                                  | green (6021)                                                            |         |

**6 Dimensions****6.1 Dimensions for the product**

|                             |          |
|-----------------------------|----------|
| Length                      | 18 mm    |
| Width                       | 21.12 mm |
| Height (without solder pin) | 19 mm    |
| Total height                | 22.5 mm  |
| Solder pin [P]              | 3.5 mm   |
| Dimension a                 | 15.24 mm |

**1017493 TDPT 2,5/ 4-SC-5,08**

---

**6.2 Dimensions for PCB design**

|                |            |
|----------------|------------|
| Hole diameter  | 1.4 mm     |
| Pin dimensions | 1 x 0,6 mm |
| Pin spacing    | 8.7 mm     |



**1017493 TDPT 2,5/ 4-SC-5,08**

## 8 Packaging information

|                    |                     |
|--------------------|---------------------|
| Type of packaging  | packed in cardboard |
| Pieces per package | 50                  |

## 9 Application

### 9.1 Temperature limit values

Ambient temperature (storage/transport)

### 9.2 Electrical data

|                                         |                            |
|-----------------------------------------|----------------------------|
| Rated current / conductor cross section | 24 A / 2.5 mm <sup>2</sup> |
| Rated insulation voltage (III/2)        | 400 V                      |
| Rated surge voltage (III/2)             | 4 kV                       |
| Contact resistance                      |                            |
| Degree of pollution                     | 2                          |

## 10 Approvals

**1017493 TDPT 2,5/ 4-SC-5,08****11 Commercial Data**

|                    |                                                      |
|--------------------|------------------------------------------------------|
| Order No.          | 1017493                                              |
| Type               | TDPT 2,5/ 4-SC-5,08                                  |
| Pieces per package | 50                                                   |
| Net weight         | 8.724 g                                              |
| GTIN               | 4055626500386                                        |
|                    | Information that applies locally, see link on page 1 |
| Country of origin  | Information that applies locally, see link on page 1 |

**12 Accessories**

| Description                                                                                                                                           | Order No. | Type          |
|-------------------------------------------------------------------------------------------------------------------------------------------------------|-----------|---------------|
| Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip | 1204517   | SZF 1-0,6X3,5 |