




File: E209153



ISO9001:2008 Certified

Mechanical Specifications (mm)

D:	31.0	± max
T:	6.0	± max
Lead Diameter	1.0	± nom
S:	7.8	± nom
L:	38.0	± nom
Coating Lead Run Down (straight Leads)	4.0	± max
B:	7.80	± nom
C:	3.22	± nom



Electrical Specifications

Resistance:	0.3	Ω	± 25 %
Max Steady State Current upto 65°C:	30.00	A	
Max Rec. Energy Rating:	100	J	
Actual Failure Instantaneous Energy:	200	J	
Maximum Capacitance @ 120 VAC:	6,946	μf	
Maximum Capacitance @ 240 VAC:	1,736	μf	
Resistance @ 100% Max Current:	0.01	Ω	
Resistance @ 50% Max Current:	0.02	Ω	
Body Temperature at 100% Max Current:	190.00	°c	
Dissipation Constant:	45.4	mw/°c	
Thermal Time Constant:	194	Sec.	
Material Type (for Beta and Curve):	A		

SL32 0R230	
Date: 11/11/2008	Drawn by: Erin Landis
Ametherm, Inc. 3111 N. Deer Run Road Carson City, Nevada USA 89701 www.ametherm.com	Approved By: Mehdi Samii
	Revision: a

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ametherm:](#)

[SL32 0R230](#)