


Hex Machine Screw Nuts

Inch

Écrous six pans pour vis de mécanique

Pouces

	THREAD	WIDTH ACROSS FLATS	THICK- NESS	STEEL	BRASS	STAINLESS	ALUMINUM
				Zinc Plated	Plain	STEEL 18-8 Plain	(Alloy 6061-T6)
				ORDER BY SPAENAU ^R NUMBERS LISTED BELOW			
     ASME/ANSI B18.6.3	0000-160	3/64"	.033"		▲HN-553		
	000-120	5/64"	.033"		▲HN-554		
	00-96	5/64"	.040"		▲HN-165B		
	00-90	5/64"	.040"		▲HN-555		
	0-80	5/32"	3/64"	HN-105	HN-105B	HN-2034	
	1-64	5/32"	3/64"		HN-106B	HN-2028	
	1-72	5/32"	3/64"	HN-107	HN-107B	HN-2027	
	*2-56	5/32"	1/16"			159-025	
	2-56	3/16"	1/16"	B-1518	HN-1B	HN-2000	
	2-64	3/16"	1/16"	HN-230	HN-2B		
	3-48	3/16"	1/16"	HN-3	HN-3B	HN-2001	
	3-56	3/16"	1/16"	HN-4	HN-4B		
	4-36	1/4"	3/32"		HN-5B		
	*4-40	3/16"	1/16"	HN-201	HN-20B		
	*4-40	3/16"	3/32"		157-002		
	4-40	1/4"	3/32"	B-753	HN-6B	HN-2002	HN-3002
	4-48	1/4"	3/32"	HN-7	HN-7B		
	*5-40	1/4"	3/32"		HN-8B		
	5-40	5/16"	7/64"	HN-205	HN-556	159-001	HN-3003
	5-44	5/16"	7/64"	HN-204	HN-526		
	*6-32	1/4"	3/32"	B-1521	HN-9B		
	6-32	5/16"	7/64"	727	HN-10B	HN-2003	HN-3004
	6-40	5/16"	7/64"	HN-11	HN-11B		
	*8-32	1/4"	3/32"	B-1522	HN-12B		
	*8-32	5/16"	7/64"	155-007	HN-19B		
	8-32	11/32"	1/8"	728	HN-13B	HN-2004	HN-3005
	8-36	11/32"	1/8"		HN-14B	HN-2036	
	10-24	3/8"	1/8"	730	HN-15B	■HN-2005	HN-3001
	10-32	3/8"	1/8"	729	HN-16B	HN-2006	HN-3017
	12-24	7/16"	5/32"	731	HN-17B	HN-2007	HN-3006
	12-28	7/16"	5/32"	B-1092			
	1/4-20	7/16"	3/16"	733	HN-18B	HN-2008	HN-3018
	1/4-28	7/16"	3/16"	734	HN-23B		
	5/16-18	9/16"	7/32"	735	HN-24B		HN-3019
	5/16-24	9/16"	7/32"	736	HN-25B		
	3/8-16	5/8"	1/4"		157-001		
*Non-standard size UNIT PACKAGE 100 All Above Listed No's. See page C8 for complete listing of Nylon Hex Nuts.				P.C. 155 Note: All sizes 0-80 to 5/16" are double chamfer and dou- ble ctsk.	P.C. 157 ▲ASTM B16-58 (Brass Specs.) Note: Mini Sizes 0000 to 1-72 not cham- fered, not ctsk. Sizes: 2-56 to 1/4" are double chamfer, double ctsk.	P.C. 159 ■159-022 316 S.S. Note: Mini Sizes 0-80 to 1-72 are not cham- fered, not ctsk. Sizes: 2-56 to 1/4"-20 are double chamfer and double ctsk. Stainless Steel Nut and Screw Asst. 805-525 on page B25.	P.C. 161 Note: HN-3003 single chamfer only. HN-3019 is single chamfer and dou- ble ctsk. Other sizes: 4-40 to 5/16" are double chamfer, double ctsk.

STEEL NOT PLATED	SQUARE NUTS ASME/ANSI B18.2.2					SQUARE Machine Screw Nuts ASME/ANSI B18.6.3			
	SPAENAU ^R No.	THREAD SIZE	NUT WIDTH A.F.	NUT THICK- NESS	UNIT PKG. QTY.	ZINC PLATED UNIT PACKAGE 100			
						SPAENAU ^R No.	THREAD SIZE	ACROSS FLAT	THICKNESS
 CLASS 2B THREAD *N-104ZP Zinc Plated P.C. 205	N-103	1/4"-20	7/16"	7/32"	100	N-25	4-40	1/4"	3/32"
	*N-104	5/16"-18	9/16"	17/64"	100	N-82	5-40	5/16"	7/64"
	N-105	3/8"-16	5/8"	21/64"	100	N-26	6-32	5/16"	7/64"
	N-106	7/16"-14	3/4"	3/8"	50	N-27	8-32	11/32"	1/8"
	N-107	1/2"-13	13/16"	7/16"	50	N-28	10-24	3/8"	1/8"
	N-109	5/8"-11	1"	35/64"	50	N-29	10-32	3/8"	1/8"
	N-110	3/4"-10	1-1/8"	21/32"	50	B-1548	1/4"-20	7/16"	3/16"
	N-111	7/8"-9	1-5/16"	49/64"	25	N-183	1/4"-28	7/16"	3/16"
	N-112	1"-8	1-1/2"	7/8"	25				
P.C. 205									

C2


SPAENAU^R

08 Mar 04

CATALOG 13