


CATALOG LISTING
19HM2-CB
 PAGE 1 OF 1
 ISSUE **M**
 3
 REPLACES
 RELEASE NO. PR-22217


REVISIONS
 A CO-1
 92286
 LJK
 22 JAN 98
 B 0004462
 KSR
 APR04
 AK
 CHECK
 JUL 96
 J A F
 CHECK
 JUL 96
 L J K
 DRAWN



- NOTES**
- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF ϕ .087 MAX ON .375 ± .002 CENTERS
 - 2 - FOR USE IN TEMPERATURE RANGE -300°F TO $+500^{\circ}\text{F}$
 - 3 - HERMETICALLY SEALED (METAL-TO-METAL, GLASS-TO-METAL)
 - 4 - ALL EXPOSED PARTS ARE OF CORROSION RESISTANT MATERIALS
 - 5 - TERMINALS ARE TINNED FOR SOLDERING
 - 6 - DO NOT: APPLY MORE THAN 1 1/2 INCH-LBS OF TORQUE WHEN TIGHTENING MOUNTING SCREWS
 - 7 - GOLD ALLOY MOVABLE CONTACT AND GOLD ALLOY STATIONARY CONTACTS

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



CHARACTERISTICS	ELECTRICAL DATA	SCALE 2 : 1	DO NOT SCALE PRINT
OPERATING FORCE --- 11.0 OZ MAX	CONTACT ARRANGEMENT SPDT	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ± WEIGHT .014 LB MAX	
RELEASE FORCE --- 1.5 OZ MIN	28 VOLTS DC RATING INDUCTIVE --- SEA LEVEL - 1/4 AMP 70,000 FT - 1/4 AMP RESISTIVE --- SEA LEVEL - 1/2 AMP 70,000 FT - 1/2 AMP		
DIFFERENTIAL TRAVEL --- .004 MAX			
OVERTRAVEL --- .006 MIN			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[19HM2-CB](#)