

Features

Regulated Converters

- 8kVDC & 10kVDC Reinforced Isolation
- Industry Standard DIP24 Package
- 6W Regulated Output
- Continuous Short Circuit Protection
- Wide Input 2:1
- Medical Approved
- EN, CSA and CB Certificates
- 2 Pinout Options
- Control Pin Option
- Efficiency to 86%

Description

The REC6 series uses a reinforced isolation transformer to offer exceptionally high isolation of 8kVDC (4kVAC/1 minute) or 10kVDC (5kVAC/1 minute) making it suitable for HT monitoring circuits, mains power meters, IGBT isolated power supplies and other sophisticated industrial and medical applications. The isolation capacitance of only 20pF makes them also suitable for low leakage applications. The isolation transformer is recognised by CSA as reinforced isolated with a minimum internal clearance of 2.4mm and a minimum internal creepage clearance of 4.6mm. The REC6 is available in two industry-standard pinouts (= "A" or "C"). Remote on/off control is possible with the /CTRL option (A pinning only) and an optional undervoltage lockout function is also available (= "X1"). The converters can deliver 140% rated power for short periods of time to cope with applications with large capacitive loads or high start up currents.

Selection Guide

Part Number DIP24	Input Voltage (VDC)	Output Voltage (VDC)	Output Current (mA)	Efficiency (%)	Max Capacitive Load ⁽¹⁾
REC6-xx05SRW/R*	9 - 18, 18 - 36, 36 - 75 4.5 - 9	5	1000	80, 81, 82 77	6800µF
REC6-xx09SRW/R*	9 - 18, 18 - 36, 36 - 75 4.5 - 9	9	667	81, 82, 83 555	6800µF
REC6-xx12SRW/R*	9 - 18, 18 - 36, 36 - 75 4.5 - 9	12	500	82, 83, 84 417	6800µF
REC6-xx15SRW/R*	9 - 18, 18 - 36, 36 - 75 4.5 - 9	15	400	84, 85, 86 333	6800µF
REC6-xx24SRW/R*	9 - 18, 18 - 36, 36 - 75 4.5 - 9	24	250	83, 84, 85 208	4700µF
REC6-xx05DRW/R*	9 - 18, 18 - 36, 36 - 75 4.5 - 9	±5	±500	80, 81, 82 77	±2200µF
REC6-xx09DRW/R*	9 - 18, 18 - 36, 36 - 75 4.5 - 9	±9	±335	81, 82, 83 ±278	±2200µF
REC6-xx12DRW/R*	9 - 18, 18 - 36, 36 - 75 4.5 - 9	±12	±250	81, 82, 83 ±208	±2200µF
REC6-xx15DRW/R*	9 - 18, 18 - 36, 36 - 75 4.5 - 9	±15	±200	82, 83, 84 ±167	±2200µF

R* = R8 or R10 for 8kVDC or 10kVDC isolation.

Note 1: Maximum capacitive load is defined as the capacitive load that will allow start up in under 1 second without damage to the converter.

* add suffix "/A" or "/C" for pinning options, see next page for details.

* add suffix "/CTRL" for control pin option (A Pinning only)

* add suffix "/X1" for Undervoltage Lockout

2:1 Input
(REC6-S_DRW/R8(R10)
xx = 4.5-9Vin = 05
xx = 9-18Vin = 12
xx = 18-36Vin = 24
xx = 36-75Vin = 48

Ordering Examples:

REC6-0512DRW/R8/A/CTRL= 5V Vin, ±12V Vout, 8kVDC isolation, pinout "A", control pin

REC6-4805SRW/R10/A = 48V Vin, 5V Vout, 10kVDC isolation, pinout "A"

REC6-1212DRW/R8/C/X1 = 12V Vin, ±12V Vout, 8kVDC isolation, pinout "C", UVL

REC6-0505SRW/R10/A/CTRL/X1 = 5V Vin, 5V Vout, 10kVDC isolation, pinout "A", control pin, UVL

ECONOLINE

DC/DC-Converter

with 3 year Warranty

RECOM


6 Watt DIP24 Reinforced Single & Dual Output



C22.2-No. 60950 Certified
C22.2-601.1 Certified
UL-60601.1 Certified

REC6/R

Derating-Graph (Ambient Temperature)



Refer to Application Notes

Specifications (measured at $T_A = 25^\circ\text{C}$, nominal input voltage, full load and after warm-up)


Input Voltage Range		2:1	
Output Voltage Accuracy		$\pm 2\%$ max.	
Line Regulation	(HL-LL)	$\pm 0.3\%$ max.	
Load Regulation	(for output load current change from 20% to 100%)	$\pm 0.6\%$ max.	
Input Surge	(1 minute)	5V types 12V types 24V types 48V types	16V max. 25V max. 50V max. 100V max.
Undervoltage Lockout	(/X1 Versions)	5V types 12V types 24V types 48V types	3.5V typ. ($\pm 20\%$) 7V typ. ($\pm 20\%$) 15V typ. ($\pm 10\%$) 32V typ. ($\pm 10\%$)
Output Ripple and Noise	(0,1 μF capacitor on output, 20MHz BW limited)	200mVp-p max.	
Transient Response	(25% step change)	1ms typ.	
Switching Frequency	(Full load and nominal input voltage)	100kHz min. / 350kHz max.	
Input Filter		Pi Network	
Capacitors	All types	MLCC capacitors only	
Minimum Load	(Operation under no load will not damage the converter, but it may not meet all specifications)	20% Full Load	
No Load Power Consumption		400mW max.	
Isolation Voltage	R8-Suffix	(tested for 1 second) (rated for 1 minute**)	8000VDC 4000VAC / 60Hz
Isolation Voltage	R10-Suffix	(tested for 1 second) (rated for 1 minute**)	10000VDC 5000VAC / 60Hz
Isolation Capacitance		20pF typ.	
Isolation Resistance		10 G Ω min.	
Short Circuit Protection	(Max operating temp. = 50°C during short circuit conditions)	Continuous, Auto Restart	
Operating Temperature Range	(free air convection)	-40°C to +75°C (see Graph)	
Case Temperature		105°C max.	
Storage Temperature Range		-55°C to +125°C	
Relative Humidity		95% RH	
Case Material		Non-Conductive Plastic	
Potting Material		Silicone	
Thermal Impedance	Natural convection	20°C/W	
Package Weight		14g	
Packing Quantity		15 pcs per Tube	
MTBF (+25°C)	Detailed Information see	using MIL-HDBK 217F	953 x 10 ³ hours
(+75°C)	Application Notes chapter "MTBF"	using MIL-HDBK 217F	234 x 10 ³ hours
EMC	Conducted Emissions	EN55022	Class A
(with 470 μF /0.1 μF capacitors across input)	Radiated Emissions	EN55022	Class A
Reinforced Isolation	Transformer Creepage	/R8 and /R10 Types	4.6 mm min.
	Transformer Clearance	/R8 and /R10 Types	2.4 mm min.
	PCB Creepage & Clearance	/R8 and /R10 Types	6.0 mm min.
	Optocoupler Creepage	/R8 and /R10 Types	6.0 mm min.
External Creepage and Clearance	Plastic Case	Input <> Output pins	14.2 mm min.
Certifications	EN Medical Safety	Report: MDD1207051 + RM1207051 Medical Report + ISO14971 Risk Assessment	EN 60601-1 3rd Edition
	IEC Medical Safety	CB-Report: CA-10168-A1-UL	IEC60601-1 3rd Edition
	CSA	Report: 2202478	C22.2 601-1 2nd Ed.
	UL	E314885-A4	UL 60601-1 3rd Edition
	General Safety	Report: 2219431	C22.2 No. 60950-1-03
	UL 60950-1 1st Ed.	Recognised as Reinforced Isolation	Supplement to Report: 2219431

**Any data referred to in this datasheet are of indicative nature and based on our practical experience only. For further details, please refer to our Application Notes.


Typical Characteristics

Efficiency vs Load

REC6-xx05SRW/R*
REC6-xx05DRW/R*




Efficiency vs Vin




REC6-xx12SRW/R*

Efficiency / Load




Efficiency VS Input Voltage




REC6-xx24SRW/R*
REC6-xx12DRW/R*

Efficiency / Load




Efficiency VS Input Voltage





Package Style and Pinning (mm) DIP 24 (continued)

"A" Pinning
/R8 & /R10



Recommended Footprint Details



Pin Connections


Pin #	Single	Dual
1 (option)	CTRL	CTRL
2	-Vin	-Vin
11	NC	-Vout
14	+Vout	+Vout
16	-Vout	Com
22	+Vin	+Vin
23	+Vin	+Vin

NC = No Connection


XX.X \pm 0.5 mm
XX.XX \pm 0.25 mm

CTRL Option



ON = Open or $0V < V_{ctrl} < 1.2V$
OFF = $2.2V < V_{ctrl} < 12V$



"C" Pinning
/R8 & /R10



Recommended Footprint Details



Pin Connections

Pin #	Single	Dual
1	+Vin	+Vin
2	+Vin	+Vin
10	NC	Com
11	NC	Com
12	-Vout	NC
13	+Vout	-Vout
15	NC	+Vout
23	-Vin	-Vin
24	-Vin	-Vin

NC = No Connection

XX.X \pm 0.5 mm
XX.XX \pm 0.25 mm