




MATERIAL LIST:

NO.	PARTS NAME	SPECIFICATION DESCRIPTION
①	CABLE	UL20276 3*(1P*28AWG+D+AL+MYLA)+7C*28AWG +AL+D+B (AL 60%) OD:6.0±0.2mm COLOR:BLACK
②	DVI CONNECTOR	DVI 12+5 MALE INSULATOR BLACK SOLDER TYPE PIN GOLD PLATED 1u" GOLD PLATED SHELL
③	HD 15P CONNECTOR	HD 15P MALE INSULATOR BLACK SOLDER TYPE PIN GOLD PLATED 1u" GOLD PLATED SHELL
④	SCREW	Ø4*47mm NICKEL PLATED
⑤	SCREW	Ø4*37.7mm NICKEL PLATED
⑥	MOLDING PVC	MOLDING PVC 063 45P COLOR:BLACK
⑦	MOLDING PVC	MOLDING PVC 063 30P COLOR:BLACK

CN1	WIRE	COLOR	CN2
C1	RED(CEN)	1	
C2	GREEN (CEN)	2	
C3	BLUE (CEN)	3	
C4	WHITE	13	
C5	R,G,B/GND	6,7,8	
6	BLACK	15	
7	RED	12	
8	BROWN	14	
14	YELLOW	9	
15	ORANGE	5,10	
16	GREEN	9	
SHELL	BRAID	SHELL	

Marking: Maxxtro C AWM E200765 STYLE 20276 80°C 30V FT2

ELECTRONIC TEST:

- A.OPEN/SHORT/INTERMITTENCE: 100%.
- B.HI-POT: 300V DC/sec
- C.INSULATION RESISTANCE: 10M ohm (MIN)
- D.CONDUCTIVE RESISTANCE: 5ohm (MAX)

ITEM NO	LENGTH	PVC COLOR	PACKING
102365	4500±100mm	BLACK 0020	BLISTER CARD

REMARK	NO	CHA.NO	SIGNATURE	DATE	SIGN	REV.	SCALE
DRAWN BY		Renzhi					
CHECKED BY							
AUDITED BY			APPROVED BY	QINGBO		A	
CRAFT			DATE	2010.11.04	PAGE	OF	

