

## Signal conditioner - MINI MCR-SL-U-I-4-SP - 2813583

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



MCR 3-way signal conditioner, for electrical isolation of analog signals, with spring-cage connection, input signal: 0 V...10 V, output signal: 4 mA...20 mA. Replacement part: 2902030 MINI MCR-2-U-I4-PT.

### Your advantages

- ✓ Power supply possible via the foot element (TBUS)
- ✓ Low power consumption
- ✓ Entry-level alternative to configurable signal conditioners
- ✓ 3-way isolation
- ✓ Fixed signal combinations
- ✓ Highly-compact isolating amplifier for electrical isolation, conversion, amplification, and filtering of standard analog signals



### Key Commercial Data

|                                      |                                                                                                         |
|--------------------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit                         | 1 pc                                                                                                    |
| GTIN                                 | <br>4 046356 101905 |
| GTIN                                 | 4046356101905                                                                                           |
| Weight per Piece (excluding packing) | 60.000 g                                                                                                |
| Custom tariff number                 | 85437090                                                                                                |
| Country of origin                    | Germany                                                                                                 |

### Technical data

#### Note

|                         |                                                                           |
|-------------------------|---------------------------------------------------------------------------|
| Utilization restriction | EMC: class A product, see manufacturer's declaration in the download area |
|-------------------------|---------------------------------------------------------------------------|

#### Dimensions

# Signal conditioner - MINI MCR-SL-U-I-4-SP - 2813583

## Technical data

### Dimensions

|        |          |
|--------|----------|
| Width  | 6.2 mm   |
| Height | 93.1 mm  |
| Depth  | 102.5 mm |

### Ambient conditions

|                                         |                                                                                   |
|-----------------------------------------|-----------------------------------------------------------------------------------|
| Ambient temperature (operation)         | -20 °C ... 65 °C                                                                  |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C                                                                  |
| Maximum altitude                        | ≤ 2000 m                                                                          |
| Permissible humidity (operation)        | 5 % ... 95 % (non-condensing)                                                     |
| Degree of protection                    | IP20                                                                              |
| Noise immunity                          | EN 61000-6-2 When being exposed to interference, there may be minimal deviations. |

### Input data

|                                   |                |
|-----------------------------------|----------------|
| Number of inputs                  | 1              |
| Configurable/programmable         | no             |
| Voltage input signal              | 0 V ... 10 V   |
| max. input voltage                | 30 V           |
| Input resistance of voltage input | approx. 100 kΩ |

### Output data

|                                 |                                  |
|---------------------------------|----------------------------------|
| Number of outputs               | 1                                |
| Configurable/programmable       | no                               |
| Current output signal           | 4 mA ... 20 mA                   |
| Max. output current             | 28 mA                            |
| Load/output load current output | ≤ 500 Ω                          |
| Ripple                          | < 20 mV <sub>PP</sub> (at 500 Ω) |

### Power supply

|                          |                                                                                                                                                                                                                 |
|--------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Nominal supply voltage   | 24 V DC                                                                                                                                                                                                         |
| Supply voltage range     | 19.2 V DC ... 30 V DC (The DIN rail bus connector (ME 6,2 TBUS-2 1,5/5-ST-3,81 GN, Order No. 2869728) can be used to bridge the supply voltage. It can be snapped onto a 35 mm DIN rail according to EN 60715)) |
| Max. current consumption | < 20 mA                                                                                                                                                                                                         |
| Power consumption        | < 450 mW                                                                                                                                                                                                        |

### Connection data

|                                  |                        |
|----------------------------------|------------------------|
| Connection method                | Spring-cage connection |
| Stripping length                 | 8 mm                   |
| Conductor cross section solid    | 0.2 mm² ... 2.5 mm²    |
| Conductor cross section flexible | 0.2 mm² ... 2.5 mm²    |

# Signal conditioner - MINI MCR-SL-U-I-4-SP - 2813583

## Technical data

### Connection data

|                             |           |
|-----------------------------|-----------|
| Conductor cross section AWG | 24 ... 12 |
|-----------------------------|-----------|

### General

|                                                        |                                                                                                                          |
|--------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------|
| No. of channels                                        | 1                                                                                                                        |
| Maximum transmission error                             | ≤ 0.1 % (of final value)                                                                                                 |
| Maximum temperature coefficient                        | < 0.01 %/K                                                                                                               |
| Temperature coefficient, typical                       | < 0.002 %/K                                                                                                              |
| Limit frequency (3 dB)                                 | approx. 100 Hz                                                                                                           |
| Step response (10-90%)                                 | approx. 3.5 ms                                                                                                           |
| Electrical isolation                                   | Basic insulation according to EN 61010                                                                                   |
| Overvoltage category                                   | II                                                                                                                       |
| Degree of pollution                                    | 2                                                                                                                        |
| Rated insulation voltage                               | 30 V AC                                                                                                                  |
| Test voltage, input/output/supply                      | 1.5 kV (50 Hz, 1 min.)                                                                                                   |
| Electromagnetic compatibility                          | Conformance with EMC directive                                                                                           |
| Noise emission                                         | EN 61000-6-4                                                                                                             |
| Noise immunity                                         | EN 61000-6-2 When being exposed to interference, there may be minimal deviations.                                        |
| Color                                                  | green                                                                                                                    |
| Housing material                                       | PBT                                                                                                                      |
| Mounting position                                      | any                                                                                                                      |
| Assembly instructions                                  | The T connector can be used to bridge the supply voltage. It can be snapped onto a 35 mm DIN rail according to EN 60715. |
| Conformance                                            | CE-compliant                                                                                                             |
| ATEX                                                   | # II 3 G Ex nA IIC T4 Gc X                                                                                               |
| UL, USA/Canada                                         | UL 508 Recognized                                                                                                        |
|                                                        | Class I, Div. 2, Groups A, B, C, D T4                                                                                    |
| GL                                                     | GL EMC 2 D                                                                                                               |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 2                                                                                                              |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 2                                                                                                              |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 2                                                                                                              |

### EMC data

|                                                        |                          |
|--------------------------------------------------------|--------------------------|
| Designation                                            | Electromagnetic RF field |
| Standards/regulations                                  | EN 61000-4-3             |
| Typical deviation from the measuring range final value | 5 %                      |
| Designation                                            | Fast transients (burst)  |
| Standards/regulations                                  | EN 61000-4-4             |
| Typical deviation from the measuring range final value | 5 %                      |

## Signal conditioner - MINI MCR-SL-U-I-4-SP - 2813583

### Technical data

#### EMC data

|                                                        |                         |
|--------------------------------------------------------|-------------------------|
| Designation                                            | Conducted interferences |
| Standards/regulations                                  | EN 61000-4-6            |
| Typical deviation from the measuring range final value | 5 %                     |

#### Standards and Regulations

|                                  |                                        |
|----------------------------------|----------------------------------------|
| Electromagnetic compatibility    | Conformance with EMC directive         |
| Noise emission                   | EN 61000-6-4                           |
| Connection in acc. with standard | CUL                                    |
| Designation                      | Electromagnetic RF field               |
| Standards/regulations            | EN 61000-4-3                           |
|                                  | EN 61000-4-4                           |
| Designation                      | Conducted interferences                |
| Standards/regulations            | EN 61000-4-6                           |
| Electrical isolation             | Basic insulation according to EN 61010 |
| Conformance                      | CE-compliant                           |
| ATEX                             | # II 3 G Ex nA IIC T4 Gc X             |
| UL, USA/Canada                   | UL 508 Recognized                      |
|                                  | Class I, Div. 2, Groups A, B, C, D T4  |
| GL                               | GL EMC 2 D                             |


#### Environmental Product Compliance

|            |                                                                                                     |
|------------|-----------------------------------------------------------------------------------------------------|
| REACH SVHC | Lead 7439-92-1                                                                                      |
| China RoHS | Environmentally Friendly Use Period = 50 years                                                      |
|            | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

### Drawings

Signal conditioner - MINI MCR-SL-U-I-4-SP - 2813583

Dimensional drawing



Classifications

eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27210100 |
| eCl@ss 4.1 | 27210100 |
| eCl@ss 5.0 | 27210100 |
| eCl@ss 5.1 | 27210100 |
| eCl@ss 6.0 | 27210100 |
| eCl@ss 7.0 | 27210120 |
| eCl@ss 8.0 | 27210120 |
| eCl@ss 9.0 | 27210120 |

ETIM

|          |          |
|----------|----------|
| ETIM 4.0 | EC002653 |
| ETIM 5.0 | EC002653 |

## Signal conditioner - MINI MCR-SL-U-I-4-SP - 2813583

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 6.0 | EC002653 |
| ETIM 7.0 | EC002653 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211506 |
| UNSPSC 7.0901 | 39121008 |
| UNSPSC 11     | 39121008 |
| UNSPSC 12.01  | 39121008 |
| UNSPSC 13.2   | 39121008 |
| UNSPSC 19.0   | 39121008 |

### Approvals

#### Approvals

##### Approvals

UL Recognized / cUL Recognized / DNV GL / cULus Recognized

##### Ex Approvals

ATEX / UL Listed / cUL Listed / EAC Ex / cULus Listed

#### Approval details

|                |                                                                                     |                                                                                                                                                       |               |
|----------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|
| UL Recognized  |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | FILE E 238705 |
| cUL Recognized |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | FILE E 238705 |
| DNV GL         |  | <a href="https://approvalfinder.dnvgl.com/">https://approvalfinder.dnvgl.com/</a>                                                                     | TAA000020N    |

## Signal conditioner - MINI MCR-SL-U-I-4-SP - 2813583

### Approvals

cULus Recognized



### Accessories

#### Accessories

##### DIN rail connector

DIN rail bus connectors - ME 6,2 TBUS-2 1,5/5-ST-3,81 GN - 2869728



DIN rail connector for DIN rail mounting. Universal for TBUS housing. Gold-plated contacts, 5-pos.

### Power module

Power terminal block - MINI MCR-SL-PTB - 2864134



MCR power terminal block for supplying several MINI Analog modules via the DIN rail connector, with screw connection, maximum current consumption of up to 2 A

Power terminal block - MINI MCR-SL-PTB-SP - 2864147



MCR feed-in terminal for supplying several MINI Analog modules via a DIN rail connector, with spring-cage connection, maximum current consumption of up to 2 A. Replacement part: 2902067 MINI MCR-2-PTB-PT.

### Power supply

## Signal conditioner - MINI MCR-SL-U-I-4-SP - 2813583

### Accessories

Power supply unit - MINI-SYS-PS-100-240AC/24DC/1.5 - 2866983



Primary-switched MINI POWER supply for DIN rail mounting, input: 1-phase, output: 24 V DC/1.5 A