




CSA rating data

AWG conductor, max. (CSA)	14
Rated (nominal) current, user group D	10 A
Rated voltage, user group D	300 V
AWG conductor, min. (CSA)	28

DIN IEC rating data

Rated voltage for overvoltage class/pollution severity III/3	160 V
Rated voltage for overvoltage class/pollution severity III/2	160 V
Rated voltage for overvoltage class/pollution severity II/2	320 V
Rated current, min. No. pins (Tu=20°C)	13 A
Rated current, max. No. pins (Tu=20°C)	12 A
Rated impulse withstand voltage for overvoltage class/pollution severity III/3	2,5 kV
Rated current, max. No. pins (Tu=40°C)	10 A
Rated current, min. No. pins (Tu=40°C)	11
Rated impulse withstand voltage for overvoltage class/pollution severity II/2	2,5 kV
Rated impulse withstand voltage for overvoltage class/pollution severity III/2	2,5 kV
Short-time withstand current resistance	3 x 1s with 72 A

Material specification

Storage temperature, max.	55 °C
Storage temperature, min.	-25 °C
Contact base material	Cu alloy
Contact surface	tinned
Insulation material	PA
Insulating material group	I
Temperature of glow-wire test	750 °C
Duration of glow-wire test	30 s
CTI	>= 600
UL 94 combustibility class	V-2
Colour	orange

System parameters

Fitting hole tolerance	+ 0.1 mm
L1 in inch	0,138 inch
L1 in mm	3,50 mm
Pitch in inch	0,138 inch
Stripping length	5 mm
No. of rows	1
Electric shock protection to DIN VDE 0470	Safe from finger touch
Volume resistance	3,6 mΩ
Dia. of fitting hole	1,3 mm
Clamping screw	M 2
Fitted by customer	yes
Max. adjacent poles per row	24
Fitted to PCB	Soldered connection
Pitch	3,50 mm
Type of screwdriver	SDI 0.4 x 2.5 - DIN 5264
Number of poles	4
Length of soldering post	3,2 mm

UL 1059 rating data

Rated voltage, user group D	300 V
AWG conductor, max. (UL 1059)	14
Rated current (UL 1059)	10 A
AWG conductor, min. (UL 1059)	28

Connectable conductors

Gauge to EN 60999 a x b; ø	2.4 mm x 1.5 mm;
Clamping range, min.	0,08 mm ²
Clamping range, max.	2,08 mm ²
fine-stranded, min. H05(07) V-U	0,5 mm ²
fine-stranded, max. H05(07) V-U	1,5 mm ²
Solid, min. H05(07) V-U	0,5 mm ²
Solid, max. H05(07) V-U	1,5 mm ²
AWG, min.	28
AWG, max.	14
O.D. of conductor insulation, max.	2,9 mm
w. plastic collar ferrule, DIN 46228 pt 4, min.	0,5 mm ²
w. plastic collar ferrule, DIN 46228 pt 4, max.	0,75 mm ²

Approvals

Rated voltage for overvoltage class/pollution severity III/3	160 V
Rated voltage for overvoltage class/pollution severity III/2	160 V
Rated voltage for overvoltage class/pollution severity II/2	320 V

Approvals

Approvals

**Classifications**

ETIM 2.0	NK
eClass 4.1	NK
eClass 5.0	NK
eClass 5.1	NK

General ordering data

Order No.	1703700000
Short text for material	LM2N 3.5/4 3.2 OR
EAN	4008190910778

- Additional colours on request
- Rated current related to rated cross-section and min. No. of poles.
- Max. O.D. of conductor: 2.9 mm
- Wire end ferrule with plastic collar to DIN 46228 pt 4
- P on drg. = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.

Related products

Order No.	Short text for material	Number of poles
1703710000	LM2N 3.5/6 3.2 OR	6
1703720000	LM2N 3.5/8 3.2 OR	8
1703730000	LM2N 3.5/10 3.2 OR	10
1703740000	LM2N 3.5/12 3.2 OR	12
1703750000	LM2N 3.5/14 3.2 OR	14
1703760000	LM2N 3.5/16 3.2 OR	16
1703770000	LM2N 3.5/18 3.2 OR	18
1703780000	LM2N 3.5/20 3.2 OR	20
1703790000	LM2N 3.5/22 3.2 OR	22
1703800000	LM2N 3.5/24 3.2 OR	24
1703810000	LM2N 3.5/26 3.2 OR	26
1703820000	LM2N 3.5/28 3.2 OR	28
1703830000	LM2N 3.5/30 3.2 OR	30
1703840000	LM2N 3.5/32 3.2 OR	32
1703850000	LM2N 3.5/34 3.2 OR	34
1703860000	LM2N 3.5/36 3.2 OR	36
1703870000	LM2N 3.5/38 3.2 OR	38
1703880000	LM2N 3.5/40 3.2 OR	40
1703890000	LM2N 3.5/42 3.2 OR	42
1703900000	LM2N 3.5/44 3.2 OR	44

1703910000	LM2N 3.5/46 3.2 OR	46
1703920000	LM2N 3.5/48 3.2 OR	48