




THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , - .
© COPYRIGHT - By - TE CONNECTIVITY		ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
CM	54	P	LTR	DESCRIPTION	DATE	DWN	APVD
			D2	REVISED PER ECR-17-018283	07FEB2018	BDA	SG

- 1 MATERIAL: CONNECTOR — NYLON UL94V-2 (RED).
CONTACTS — 0.30[.012] THICK COPPER ALLOY
(BRIGHT TIN-LEAD 0.00203[.000080] MIN. THICK
FOR CONTACTS 644467-2 THRU 1-644467-4]
(MATTE WHISKER MITIGATED TIN 0.00203[.000080] MIN
THICKNESS OVER NICKEL UNDERPLATE FOR
3-644467-2 THRU 4-644467-4).
- 2 CONTACTS ACCEPT 22 AWG WIRE WITH 2.41[.095] MAX INSULATION DIAMETER.
- 3 CONTACTS MUST ACCEPT 1.14 ± 0.03 [$0.045 \pm .001$] SQUARE POST AND REMAIN LOCKED
IN POSITION.
- 4 IDENTIFICATION NUMBER FOR LAST CIRCUIT MAY NOT APPEAR ON ALL ASSEMBLIES.
- 5 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 6 HOUSING FEATURES ARE: FEED-THRU WITH LOCKING RAMP AND POLARIZING TAB.
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 8 OBSOLETE PARTS



		55.47	[2.184]	14	4-644467-4
		51.51	[2.028]	13	4-644467-3
		47.55	[1.872]	12	4-644467-2
		43.59	[1.716]	11	4-644467-1
		39.62	[1.560]	10	4-644467-0
		35.66	[1.404]	9	3-644467-9
		31.70	[1.248]	8	3-644467-8
		27.74	[1.092]	7	3-644467-7
		23.77	[.936]	6	3-644467-6
		19.81	[.780]	5	3-644467-5
		15.85	[.624]	4	3-644467-4
		11.89	[.468]	3	3-644467-3
		7.92	[.312]	2	3-644467-2
Δ_7	SUPERSEDED	55.47	[2.184]	14	1-644467-4
Δ_7	SUPERSEDED	51.51	[2.028]	13	1-644467-3
Δ_8	SUPERSEDED	47.55	[1.872]	12	1-644467-2
		43.59	[1.716]	11	1-644467-1
		39.62	[1.560]	10	1-644467-0
		35.66	[1.404]	9	644467-9
Δ_7	SUPERSEDED	31.70	[1.248]	8	644467-8
Δ_7	SUPERSEDED	27.74	[1.092]	7	644467-7
Δ_8	SUPERSEDED	23.77	[.936]	6	644467-6
		19.81	[.780]	5	644467-5
		15.85	[.624]	4	644467-4
		11.89	[.468]	3	644467-3
		7.92	[.312]	2	644467-2
		DIM A		NO. OF CIRCUITS	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. LEWIS 12 FEB 91		 TE Connectivity				
		CHK R. SWING 12 FEB 91						
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD D. CLARK 20 FEB 91				
		PRODUCT SPEC 108-1051		NAME MTA 156 CONNECTOR ASSEMBLY, 22 AWG, STANDARD -				
		APPLICATION SPEC 114-1020						
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
				A2	00779	C-644467	-	
CUSTOMER DRAWING						SCALE 4:1	SHEET 1 OF 1	REV D2