







LOC	DIST	REVISIONS					
CM	53	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A1	REVISED PER ECO-11-004917	12MAR2011	RK	HMR



RECOMMENDED CUT OUT
FOR 2.00[.079] MAX. THICK PANEL



1 NYLON, UL94V-2, NATURAL.

2 DIMENSION TO BE CHECKED AT SURFACE A.

3. DIMENSIONS IN BRACKETS ARE IN INCHES.

4. MALE CONTACTS MUST BE INSERTED SO THAT THE TOP OF THE WIRE AND INSULATION CRIMPS ARE FACING THE SIDE OF THE HOUSING WITH THE LOCKING LATCH.

5. RECOMMENDED MAX. PANEL THICKNESS 2.00[.079].

6. PANEL MUST BE PUNCHED SO THAT THE HOUSING ENTERS THE PANEL IN THE SAME DIRECTION AS THE PUNCH.

52.3[2.059]	51.6[2.032]	52.00[2.047]	24	2-794550-4
48.1[1.894]	47.4[1.866]	47.80[1.882]	22	2-794550-2
43.9[1.728]	43.2[1.701]	43.60[1.171]	20	2-794550-0
39.7[1.563]	39[1.535]	39.40[1.551]	18	1-794550-8
35.5[1.398]	34.8[1.370]	35.20[1.386]	16	1-794550-6
31.3[1.232]	30.6[1.205]	35.00[1.220]	14	1-794550-4
27.1[1.067]	26.4[1.039]	26.80[1.055]	12	1-794550-2
22.9[.902]	22.2[.874]	22.60[.889]	10	1-794550-0
18.7[.736]	18.00[.709]	18.40[.724]	8	794550-8
14.5[.571]	13.8[.543]	14.20[.559]	6	794550-6
10.3[.406]	9.6[.378]	10.00[.394]	4	794550-4
6.1[.240]	5.4[.213]	5.80[.228]	2	794550-2
C	B	A	NO. OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN R. VESTAL	16MAR99	 TE Connectivity			
DIMENSIONS: mm[INCHES]				CHK R. SWING	16MAR99				
TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD C. CASH	16MAR99	PLUG, PANEL MOUNT, 2 TO 24 POSITION, AMP-NUACTM POWER CONNECTOR			
9 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH				PRODUCT SPEC - APPLICATION SPEC					
MATERIAL				WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
				-		A1	00779	C=794550	-
CUSTOMER DRAWING						SCALE	4:1	SHEET	1 OF 1
						REV	A		

