



PLT2.5H-L



- For indoor use
- Versatile cable ties can be used in countless applications
- One-piece construction for consistent performance and reliability
- Lowest threading force of any one-piece cable tie in the industry
- A variety of materials and colors available for specific applications
- Miniature to Standard cross sections feature a curved tip for easy threading and handling

■ Part Number	PLT2.5H-L
■ RoHS Compliancy Status	Compliant
■ Part Description	Cable Tie, 9.8", Light-Heavy cross section
■ Product Type	Cable Ties
■ Material	Nylon 6.6
■ Color	Natural
■ CSA Certified	Yes
■ UL Listed (File #E56854)	Yes
■ UL Recognized (File #E56854)	Yes
■ Length (In.)	9.8
■ Length (mm)	251
■ Width (In.)	.300
■ Width (mm)	7.6
■ CE Compliant	Yes
■ Cross Section	Light-Heavy
■ Head Height (In.)	.290
■ Head Height (mm)	7.4
■ Head Width (In.)	.480
■ Head Width (mm)	12.2
■ Locking Style	Locking
■ Material Flammability Rating	UL 94V-2
■ Max. Bundle Diameter (In.)	2.50
■ Max. Bundle Diameter (mm)	64
■ Max. Continuous Use Temperature	185°F (85°C)
■ Min. Loop Tensile Strength (Lbs.)	120
■ Min. Loop Tensile Strength (N)	534

■ Pricing Description	Cable Tie, 9.8"L (251mm), Light-Heavy, Nylon, Natural
■ Thickness (In.)	.075
■ Thickness (mm)	1.9
■ Tool	GTH, GS4H, GS4EH, PTH, STH2, ST3EH
■ Min. Order UOM	PC
■ Min. Order Qty.	50
■ BOM Qty. (# of Pkgs.)	

NOTES:

- SS_5540_00.PRT

										PANDUIT	CORP. TINLEY PARK, ILLINOIS	
										PAN-TY CABLE TIES PLT SERIES		
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .0000 (.XXX) ± .020(.51) (.XX) ± .02(.5) ANGLES ± .0000	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
										DRAWN BY SO	MAT'L:	
										DATE 12-27-84	NYLON 6/6	
										CHK'D HVP	DRAWING NO. SS-5540 SHEET 4	
											DWG A SIZE	
REV	DATE	BY	CHK	DESCRIPTION				ECN - R	CUST	SUP		
7	7/3/03	JABO		ADDED C REF DIMENSION TO TIE. C DIM. WAS ALREADY IN MATRIX.				5540	7			