



This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.


MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



ORIENTATION



CIRCUIT



NOTE:
1. SUPPLIED WITH SILVER PLATED
HEX NUT AND LOCK WASHER.

MIN. CAP. (pF)	WORKING VOLTAGE (WVdc)	CURRENT IDC	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD -220			
	125 °C		50 MHz	100 MHz	1 GHz	10 GHz
1500	200	10 A	32	45	70	70

X-2015 Rev-0	REVISION RECORD	Original Release C.O. ECO-666	A	TOLERANCES unless otherwise specified 2 PLC. DECIMAL $\pm$ $\frac{\quad}{\quad}$ 3 PLC. DECIMAL $\pm$.031 [0.79] ANGLES $\pm$ $\frac{\quad}{\quad}$	Title M15733/61-0006 BUSHING STYLE EMI FILTER	
					Drawn L.E. 04-15-09	Scale X 3
					Approved R.L. 04-15-09	
					TUSONIX TUCSON, ARIZONA	A 4203-501

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix:](#)

[4203-501](#)