



NOTES: 1. MATERIALS AND FINISHES: REVERSE POLARITY TNC BULKHEAD CRIMP JACK - P/N: 122532RP MICRO COAX PLUG TERMINATED USING 1.37 MM CABLE - P/N: 100909-01	336206-14-XXXX		REVISIONS			
	DRAWING NO.	REV	DESCRIPTION	DATE	ECO	APPR
	THIRD ANGLE PROJ. 	A	RELEASE TO MFG.	24-Nov-10	--	KR
		B	SEE SHEET 1	27-Mar-14	2716	KR/BCG

2. ELECTRICAL:

 A. IMPEDANCE: 50 OHM, NOMINAL
3. PACKAGING:

 A. QUANTITY: SINGLE PACK
 B. BAG TO BE MARKED: AMPHENOL RF, 336206-14-XXXX, AND DATE CODE
- 
SCALE 1.000



ORDERING INFORMATION	
PART NUMBER (METRIC)	LENGTH IN INCHES * [METERS]
336206-14-0050	1.97 [0.050]
336206-14-0075	2.95 [0.075]
336206-14-0100	3.94 [0.100]
336206-14-0150	5.91 [0.150]
336206-14-0200	7.87 [0.200]
336206-14-0250	9.84 [0.250]
336206-14-0300	11.81 [0.300]

TOLERANCE TABLE	
LENGTH IN INCHES/FT [METERS]	TOLERANCE
0" - 23.90" [0 - 0.607]	±0.25" [0.006]
24.00" - 59.00" [0.610 - 1.499]	±0.50" [0.013]
5.0' - 24.9' [1.524 - 7.617]	±2.5%
25.0' & UP [7.620 & UP]	±5.0%

* ADDITIONAL LENGTHS CAN BE PROVIDED.
CONTACT AMPHENOL RF MARKETING FOR QUOTE

CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

DESIGN REQUIREMENTS:

☒ FREQUENCY: DC TO 6.0 GHz

☐ VSWR _____ : 1 MAX

☐ INS. LOSS _____ dB MAX

☒ CONTINUITY

☒ HI-POT :200 VRMS

☐ OTHER

UNLESS OTHERWISE SPECIFIED, TOLERANCES ARE AS FOLLOWS: 2 PLACE DECIMAL 3 PLACE DECIMAL ANGLES ±.015 (0,381 mm) ±.005 (0,127 mm) ± 1°	MATERIAL SEE NOTES	DRAWN KARTHIK R	DATE 24-Nov-10	TITLE REVERSE POLARITY TNC BULKHEAD CRIMP JACK TO MICRO COAX PLUG TERMINATED, USING 1.37MM CABLE VARIOUS LENGTHS		Amphenol Connex	
		ENGINEER KARTHIK R	DATE 24-Nov-10				
	REFERENCE	APPROVED B.C. GLEISSNER	DATE 27-Mar-14	SCALE: 4.0:1		SHEET	2 OF 2
		CAD FILE		DWG SIZE	DRAWING NO. 336206-14-XXXX	REV B	