




## Features

- Surface mount
- Compact mini-size - 5 x 7.2 mm
- Economical
- Low capacitance and insertion loss
- UL Recognized 
- RoHS compliant\*

## 2054 Series Surface Mount Gas Discharge Tube Surge Protector

Bourns offers a low-cost, 3-electrode surface mount GDT surge protection device. The 2054 Series is ideal for broadband protection due to its ultra-low capacitance. The 2054 Series offers superior protection characteristics suitable for telecommunications, commercial and industrial applications.

### Characteristics

Test Methods per ITU-T (CCITT) K.12, IEEE C62.31

| Characteristic                    | Model No. |         |         |         |         |
|-----------------------------------|-----------|---------|---------|---------|---------|
|                                   | 2054-23   | 2054-30 | 2054-35 | 2054-42 | 2054-47 |
| DC Sparkover $\pm 20\%$ @ 100 V/s | 230 V     | 300 V   | 350 V   | 420 V   | 470 V   |
| Impulse Sparkover <sup>(1)</sup>  |           |         |         |         |         |
| 100 V/ $\mu$ s                    | 550 V     | 700 V   | 700 V   | 800 V   | 800 V   |
| 1000 V/ $\mu$ s                   | 650 V     | 800 V   | 800 V   | 900 V   | 900 V   |

<sup>(1)</sup> Impulse Sparkover voltage is defined as typical values of distribution.

|                                          |                                |                           |
|------------------------------------------|--------------------------------|---------------------------|
| Insulation Resistance (IR) .....         | 100 V .....                    | >10 <sup>9</sup> $\Omega$ |
| Capacitance.....                         | 1 MHz.....                     | 2.0 pF maximum            |
| DC Holdover Voltage <sup>(2)</sup> ..... | >135 V (80 V for 2054-23)..... | <150 ms                   |
| Impulse Discharge Current.....           | 5000 A, 8/20 $\mu$ s .....     | 5 operations              |
|                                          | 200 A, 10/1000 $\mu$ s .....   | 100 operations            |
| Alternating Discharge Current .....      | 5 Arms, 1 sec., 50 Hz .....    | 1 operation minimum       |
| Operating Temperature.....               |                                | -30 to +85 °C             |
| Climatic Category (IEC 60068-1).....     |                                | 40/90/21                  |

#### Notes:

- **UL Recognized component, UL File E153537.**
- Line to Line voltage is approximately 1.8 to 2 times the stated Line to Ground voltage.
- The rated discharge current is the total current equally divided between each line to ground.
- Surface Mount (SM) parts may show a temporary increase in DCBD after the solder reflow process. Most devices will recover within 24 hours time. It should be noted that there is no quality defect nor change in protection levels during the temporary change in DCBD.
- At delivery AQL 0.65 AQL Level II, DIN ISO 2859
- Bourns recommends reflowing surface mount devices per IPC/JEDEC J-STD-020 rev D.

<sup>(2)</sup> Network applied.

**BOURNS®**

**Asia-Pacific:** Tel: +886-2 2562-4117 • Fax: +886-2 2562-4116

**EMEA:** Tel: +36 88 520 390 • Fax: +36 88 520 211

**The Americas:** Tel: +1-951 781-5500 • Fax: +1-951 781-5700

**www.bourns.com**

\*RoHS Directive 2002/95/EC Jan. 27, 2003 including annex and RoHS Recast 2011/65/EU June 8, 2011.


Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.


## 2054 Series Surface Mount Gas Discharge Tube Surge Protector

**BOURNS®**

### Product Dimensions



### Recommended Pad Layout



### How to Order

**2054 - xx - SM - RP LF**

Model Number Designator \_\_\_\_\_

Voltage (Divided by 10) \_\_\_\_\_

Surface Mount \_\_\_\_\_

Packaging \_\_\_\_\_


RoHS Compliance \_\_\_\_\_

RP = Reel Pack

LF = RoHS Compliant Product

### Packaging Specifications

Model 2054-xx-SM-RPLF (Reel Pack) contains 900 pieces per reel, 2,700 pieces per box. The reel is 330 mm in diameter and 18 mm wide.



REV. F 08/15

Specifications are subject to change without notice.  
The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.  
Users should verify actual device performance in their specific applications.