

Technical drawing of a mechanical part, showing top and side views with dimensions in inches and millimeters.

**Top View Dimensions:**

- Overall width: 12.70 [500] SQ.
- Distance from center to corner hole center: 8.64 [.340]
- Distance from center to corner hole center (horizontal): 8.64 [.340]
- Distance from center to corner hole center (vertical): 8.64 [.340]
- Corner hole diameter:  $\phi 2.60$  [ $\phi .102$ ](4X)

**Side View Dimensions:**

- Overall height: 26.90 [1,060]
- Distance from base to top of main body: 19.00 [.749]
- Distance from base to top of main body (inner): 5.00 [.197]
- Distance from base to top of main body (outer): 2.00 [.079]
- Distance from base to top of main body (inner): 7.90 [.311]
- Distance from base to top of main body (outer): 4.75 [.187]
- Distance from base to top of main body (inner): 4.10 [.162]
- Distance from base to top of main body (outer): 1.27 [.050]

**Part Identification:**

7/16-28UNEF-2A