




NOTES:

1. MATERIALS: TEFLON MIL-P-19468, BRASS QQ-B-620, BERYLLIUM COPPER QQ-C-530, COPPER WIRE QQ-W-330, SILKONE RUBBER ZZ-R-705 COLOR RED.
2. PLATING: SILVER PLATE QQ-S-365 .0002 MIN.
3. ELECTRICAL CHARACTERISTICS:
 NOMINAL IMPEDANCE: 50 Ω .
 WORKING VOLTAGE: 500 VOLTS RMS.
 FREQUENCY RANGE DC TO 4GHz.
 INSULATION RESISTANCE: 5000 MEGOHMS MIN.
 DIELECTRIC WITHSTANDING VOLTAGE: 1500 VOLTS RMS.

REVISIONS

ISSUE	CHANGES
7	CN 18684 C ATT 30 OCT 79

SCALE: 4:1

USED ON:

REF:

FINISH

SPEC. / CER 10004

MATL

SPEC.

TNC (F) / BNC (M)
ADAPTER

DRAWN / M

DATE / 5 NOV 77

APPR. /

DATE / 5 NOV 77

KINGS ELECTRONICS
40 MARBLEDALE ROAD
TUCKAHOE, N. Y. 10707

KA-91-10

UNLESS OTHERWISE SPECIFIED:

1. TOLERANCES: FRACTIONS & 2 PLACE DECIMALS $\pm .010$
 3 PLACE DECIMALS $\pm .004$
 T. I. R. CONCENTRICITY OF ANY 2 DIAMETERS MAY NOT EXCEED HALF THE SUM OF THEIR TOLERANCES.
2. REMOVE ALL BURRS, BREAK SHARP EDGES .005 MAX.
3. NO FILLETS PERMITTED.
4. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX.
5. ALL DIMENSIONS PRIOR TO PLATING.

S-D