




Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de © FCI ELECTRONICS. Copyright FCI ELECTRONICS INC.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of © FCI ELECTRONICS. Copyright FCI ELECTRONICS INC.



PRODUCT NO.
57496

- NOTE: 1. PRINT IS FOR ASSEMBLY REFERENCE ONLY.
2. P/N'S WITH SUFFIX "LF" ARE LEAD FREE P/N'S
3. HOUSING COLOR OF CABLE ASSEMBLY KIT
-P/N 57496-101/101LF: WHITE
-P/N 57496-102/102LF: BLACK
HOUSING: HIGH TEMP RESIN WITH UL 94V-0
4. CONTACT
MATERIAL : HIGH STRENGTH COPPER ALLOY
FINISH: 30u" Au MIN. OVER 50u" NICKEL UNDERPLATE
SHIELD:
MATERIAL : HIGH STRENGTH COPPER ALLOY
FINISH: 100u" MIN. T/L OVER 50u" NICKEL UNDERPLATE MIN.
100u" MIN. PURE TIN OVER 50u" NICKEL UNDERPLATE MIN.
FOR LEAD FREE P/N'S
5. APPLICABLE CABLE SIZE : Ø4.0 TO Ø6.5 mm
6. PACKAGING : EACH PACK IN SPECIFIC PLASTIC BAG,
PLUG: 300 PCS/BAG
MATING SHIELD: 300 PCS/BAG
REAR SHIELD: 300 PCS/BAG
7. PACKING STANDARD GS-14-920 WILL BE APPLIED FOR LEAD FREE P/N'S
8. FOR LEAD FREE P/N, THE PRODUCT MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008
9. FOR LEAD FREE P/N, THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 40 SECONDS IN A CONVECTION, INFRARED OR VAPOR PHASE REFLOW OVEN.
10. INSULATION MYLAR MUST COVER WITH ALL TERMINALS AND SOLDERED POINTS ON BOTH TWO SIDES (ONE PIECE ON EACH SIDE) AFTER SOLDERING AND BEFORE ASSEMBLE SHIELDS. THE RECOMMENDED DIMENSION OF MYLAR IS 10.00+/-0.10mm WIDTH , 6.00+/-0.10mm LENGTH, 0.10+/-0.03mm THICKNESS, AND IT MUST BE OF HIGH TEMPERATURE RESISTANCE.




mat'l. code NOTE 1 & 2				tolerances unless otherwise specified		CUSTOMER COPY	FCI www.fciconnect.com	
ltr	ecn no	dr	date	linear	.X ±0.30	projection 	title USB+POWER	
A	T10382	WL	12/27/01		.XX ±0.20			
B	T20235	WL	07/29/02		.XXX±0.10			
C	N05-0024	PH	01/31/05	angles		mm 	product family size dwg no USB 57496	
D	N08-0122	Bobby Si	06/16/08	dr	WENDY CHEN 10/16/01			
				enrg	R Y LIU 10/16/01			
				chr	R Y LIU 10/16/01	scale 2:1	A4	code TWN sheet 1 of 2
				appd	JENN TSAO 10/16/01			
sheet index	revision sheet							

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire.
Propriete de FCI ELECTRONICS INC. Droits de reproduction FCI ELECTRONICS INC.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI ELECTRONICS INC. Copyright FCI ELECTRONICS INC.



PRODUCT NO.
57496



SECTION A-A

mat'l. code NOTE 1 & 2				tolerances unless otherwise specified			CUSTOMER COPY		 www.fciconnect.com						
ltr	ecm no	dr	date	linear	.X ±0.30			projection 	title USB+POWER						
D					.XX ±0.20										
					.XXX±0.10										
				angles					product family USB				code		
				dr	WENDY CHEN	10/16/01	scale 2:1		size dwg no				TWN		
				enr	R Y LIU	10/16/01			A4 57496				sheet		
				chr	R Y LIU	10/16/01						2 of			
				appd	JENN TSAO	10/16/01									
sheet index	revision sheet														